

Protect It! 4-Outlet Desktop-Grommet Surge Protector, 10 ft. Cord, 1500 Joules, 2 USB Charging Ports, Black Housing

MODEL NUMBER: TLP410DMUSB



Installs in your desktop's pre-cut grommet to safeguard your computer, scanner and other electronics against surges, spikes and line noise, as well as charge mobile devices, including smartphones, tablets and MP3 players.

Description

The TLP410DMUSB Protect It!® 4-Outlet Surge Protector features four NEMA 5-15R outlets and a surge suppression rating of 1500 joules to protect your components against surges, spikes and EMI/RFI line noise that can damage sensitive electronics and destroy data. Plus, two USB ports produce 2.4A of combined power to charge your mobile devices, such as smartphones, tablets and MP3 players. Recommended for home or office workstations, the TLP410DMUSB is designed for installation in your desktop's 60-millimeter (2.4 inches) grommet hole (if your desk has no pre-cut hole, you can drill one yourself). It folds onto the desktop for connection of equipment. An LED indicates surge suppression at a glance. A resettable 15A circuit breaker shuts down equipment in case of an overload. When not in use, straighten the TLP410DMUSB to a vertical position and push it down into the grommet until it's flush with the desk surface. The 10-foot (3.1-meter) power cord is long enough to reach distant AC outlets. Permanent mounting to the desk helps deter theft. Tripp Lite will repair or replace any connected equipment damaged by surges up to \$20,000 for life (valid in the U.S., Canada and Puerto Rico only).

Features

Powers and Protects Electronic Components

- 4 NEMA 5-15R outlets accept most computers and peripherals
- 1500 joules of surge suppression protect against surges, spikes and EMI/RFI line noise
- Easy-to-read LED indicates surge suppression at a glance
- Resettable 15A circuit breaker protects against overloads
- Recommended for home or office workstations

Powers and Charges Mobile Devices

- 2 USB ports (2.4A total) charge smartphones, tablets and other devices

Mounts Safely in Desktop's Grommet Hole

- Designed for installation in 60 mm grommet
- Folds onto desktop for connecting equipment
- Pushes into the grommet hole flush with desktop when not in use

Highlights

- Pushes down flush with desktop surface when not in use
- 4 NEMA 5-15R outlets and 2 USB charging ports (2.4A total)
- 1500 joules of surge suppression
- Designed for installation in 90 mm grommet
- 10 ft. power cord reaches distant AC outlets

Package Includes

- TLP410DMUSB Protect It! 4-Outlet Desktop-Grommet Surge Protector
- Owner's manual



Powering Business Worldwide



- 10 ft. power cord stores away out of sight under the desk
- Permanent mounting to the desk helps deter theft

\$20,000 Ultimate Lifetime Insurance

- Tripp Lite will repair or replace any connected equipment damaged by surges up to \$20,000 for life
- Valid in the U.S., Canada and Puerto Rico only

Specifications

OVERVIEW	
UPC Code	037332199638
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Strip
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	



Powering Business Worldwide



Number of Charging Ports	2
Total Charging Watts	12
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.4A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1500
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400,500,500
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	4.20 x 3.00 x 12.00
Shipping Dimensions (hwd / cm)	10.67 x 7.62 x 30.48
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
Unit Dimensions (hwd / in.)	11.540 x 2.250 x 2.360
Unit Dimensions (hwd / cm)	29.31 x 5.72 x 5.99
Unit Weight (lbs.)	1.74
Unit Weight (kg)	0.79
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No



Powering Business Worldwide



Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1449; UL 962A
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.