

2-Port USB 3.0 SuperSpeed Desktop Extension Cable A (M/2xF), 6 ft. (1.83 m)

MODEL NUMBER: U324-006-DSK2



Converts your computer's USB 3.0 port to 2 USB 3.0 ports and extends them up to 6 ft away. Ideal for connecting thumb drives, digital cameras and other USB-A devices.

Features

Expands an Existing USB 3.0 Port to 2 Ports and Extends Them an Extra 6 ft.

- Move a hard-to-reach USB port within easy access
- Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices
- Features one USB 3.0 data/power port and one power-only port

Enjoy SuperSpeed Transfer Rates in High-End Applications

- Supports data transfer rates up to 5 Gbps—10x the speed of USB 2.0
- Bi-directional interface allows data to flow both directions at the same time, increasing theoretical bandwidth by 10x
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding blocks EMI/RFI interference
- Molded nickel-plated connectors ensure excellent connectivity
- Integral strain relief for cable and connectors' long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces
- Black padded non-sliding base

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332199478 |

Highlights

- Supports data transfer rates up to 5 Gbps
- Bi-directional interface allows data to flow both directions
- Backward compatible with previous USB generations
- Features one USB 3.0 data/power port and one power-only port
- Double-shielded protection against EMI/RFI line noise
- Black padded non-sliding base

System Requirements

- Computer, laptop or other device with USB 3.0 port (to achieve USB 3.0 speeds)

Package Includes

- U324-006-DSK2 2-Port USB 3.0 SuperSpeed Desktop Extension Cable (M/2xF), 6 ft.



Powering Business Worldwide



| | |
|---------------------------------------|------------------------------|
| Technology | USB 3.x |
| Cable Type | Passive |
| INPUT | |
| Maximum Input Amps | 2 |
| CONNECTIONS | |
| Side A - Connector 1 | USB A (MALE) |
| Side B - Connector 1 | (2) USB A (FEMALE) |
| Connector Plating | Nickel |
| Contact Plating | Gold |
| Connector Style | Straight |
| CHARGING | |
| Total Charging Watts | 10 |
| PHYSICAL | |
| Material of Construction | PVC |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Outer Diameter (OD) | 5.5mm |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 5.31 x 3.94 x 0.50 |
| Shipping Dimensions (hwd / cm) | 13.49 x 10.01 x 1.27 |
| Shipping Weight (lbs.) | 0.24 |
| Shipping Weight (kg) | 0.11 |
| Unit Packaging Type | Polybag |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 104°F (0° to 40°C) |
| Storage Temperature Range | 14° to 131°F (-10° to 55°C) |
| Relative Humidity | 5% to 90% RH, Non-Condensing |
| Operating Humidity Range | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range | 0% to 90% RH, Non-Condensing |
| Power Provided to Connected Device(s) | 10W (5V/2A) |



Powering Business Worldwide



| FEATURES & SPECIFICATIONS | |
|-------------------------------------|---|
| Over Current Protection | Yes |
| USB Specification | USB 3.2 Gen 1 (up to 5 Gbps) |
| Data Transfer Rate | 5 Gbps |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA); UKCA |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.