



Powering Business Worldwide

4-in-1 Battery Charger

MODEL NUMBER: UBC41



Versatile dual-input voltage battery charger compatible with any lead acid battery, including gel-type, maintenance-free, AGM and Ni-MH. Ideal for workbenches, construction sites, warehouses and other workspaces.

Description

The versatile UBC41 4-in-1 Battery Charger has many uses from charging the dead battery in your automobile or golf cart to various fleet and industrial operations. Compatible with any lead acid battery, including gel-type, maintenance-free, absorbent glass mat (AGM) and Ni-MH, the UBC41 operates on either 120V or 240V AC input mains voltage at an automatically selected 50 Hz or 60 Hz. The charger works with 12-, 24-, 36- or 48-volt batteries at high or low charge rates. Use the included alligator clips to connect the charger to the battery.

LED display monitors charge rate, battery capacity and float status. It also informs you of charging errors, such as a blown fuse, at a glance. Built-in cooling fan and automatic shutdown feature protect the unit from overheating. The charger is also protected from short circuits and accidental reverse connections.

The rugged aluminum housing is designed to handle day-to-day stress. Built-in mounting feet allow the UBC41 to be permanently installed on any rigid horizontal surface with user-supplied hardware.

Features

Digital Power Electronics for Accurate, Reliable Operation

- All-in-one charger compatible with 12V, 24V, 36V and 48V batteries
- Selectable high and low charge rates (H/L 12V/24V: 30A/10A; 36V: 25A/10A; 48V: 15A/7A)
- Selectable 120V or 240V input mains voltage
- Automatically selects 50 Hz or 60 Hz

Charges Lead Acid Batteries

- Including gel-type, maintenance-free, AGM and Ni-MH
- Comes with alligator clips for connection

Highlights

- Charges 12V, 24V, 36V and 48V batteries
- Selectable 120V or 240V input mains voltage (50/60 Hz)
- Compatible with lead acid batteries
- Easy-to-read LED display monitors charge status
- Keeps battery at full capacity without overcharging

Package Includes

- UBC41 4-in-1 Battery Charger
- Alligator clips with cable
- Power cord with NEMA 5-15P plug
- Owner's manual



Powering Business Worldwide

Easy-to-Read LED Display

- Yellow and green LEDs monitor charge rate, battery capacity and float status
- Red LED alerts you to overheating, wrong battery voltage and other charging errors

Protection Functions

- Shuts down automatically upon overheating, and restarts when cooled to appropriate temperature
- Won't operate when battery connectors are attached in reverse

Durable Construction

- Rugged aluminum housing stands up to daily use
- Built-in mounting feet allow installation on any rigid horizontal surface

Specifications

OVERVIEW	
UPC Code	037332191533
Accessory Type	Battery Charger
Accessory Class	Power Inverter Accessories
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 240V AC
Input Connection Type	NEMA 5-15P power cord
OUTPUT	
Frequency Compatibility	50 / 60 Hz
BATTERY	
Battery Charge	Selectable high and low charge rates (H/L 12V/24V: 30A/10A; 36V: 25A/10A; 48V: 15A/7A)
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Yellow and green LEDs monitor charge rate, battery capacity and float status. Red LED alerts you to overheating, wrong battery voltage and other charging errors.
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Shipping Dimensions (hwd / in.)	6.92 x 10.11 x 14.80
Shipping Dimensions (hwd / cm)	17.58 x 25.68 x 37.59
Shipping Weight (lbs.)	11.30



Powering Business Worldwide

Shipping Weight (kg)	5.13
Unit Dimensions (hwd / in.)	3.960 x 8.780 x 11.810
Unit Dimensions (hwd / cm)	10.06 x 22.30 x 29.99
Unit Weight (lbs.)	9.7
Unit Weight (kg)	4.40
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.