

Portable Charger - USB-A, 2600mAh Power Bank, Lithium-Ion, Black

MODEL NUMBER: UPB-02K6-1U



Charge your mobile device anywhere, anytime without plugging into an AC power outlet. Ideal for cellphones, smartphones, tablets, e-readers, MP3 players and Bluetooth speakers, headsets and headphones.

Description

No more frantic searching for an AC power outlet when your cellphone, tablet or other mobile device's battery power is getting low. The UPB-02K6-1U Portable 2600mAh Mobile Power Bank is the perfect power solution when you're on the road, or stuck somewhere without convenient electricity. It fits comfortably in your pocket, purse, backpack or laptop bag to keep your e-reader, MP3 player, handheld game console or Bluetooth device operating when you need it.

Just connect your device to the UPB-02K6-1U's USB-A port using the included USB Micro-B cable or another cable suitable for your device. The LED indicator will blink to indicate the Mobile Power Bank has enough power to charge the device. The LED will turn off when the Mobile Power Bank's built-in lithium-ion battery drops below 5%.

The portable UPB-02K6-1U provides up to 5V, 1A of power, and its 2600mAh capacity charges devices at maximum power up to 2.6 hours. It protects against short circuits, overvoltage, over-current, overcharges and overdischarges. Charge the Mobile Power Bank by connecting its USB Micro-B port to a USB charger or a computer's USB-A port using the included cable. The blinking LED indicator will turn solid when the battery reaches 100% capacity.

Features

Travel-Sized for Convenient Charging Anywhere

- Fits comfortably in your pocket, purse, backpack or laptop bag
- Ideal for charging cellphones, tablets, e-readers, MP3 players, handheld game consoles and Bluetooth headsets, headphones and speakers
- USB Micro-B charging cable included

Superior Charge Capability Without an AC Power Outlet

- Connect USB-A port to device for charging at maximum output up to 2.6 hr.
- Provides up to 5V, 1A of power at 2600mAh capacity
- Protects against short circuits, overvoltage, over-current, overcharges and overdischarges

Built-In Lithium-Ion Battery

- Connect the power bank's USB Micro-B port to a USB charger or a computer's USB-A port to charge

Highlights

- Fits comfortably in your pocket, purse, backpack or laptop bag
- Provides up to 5V, 1A for charging mobile devices
- LED indicates low or full lithium-ion battery
- Charges devices at maximum output up to 2.6 hr.
- Includes USB Micro-B charging cable

Package Includes

- UPB-02K6-1U Portable 2600mAh Mobile Power Bank USB Battery Charger
- USB Micro-B cable, 3 ft.
- Owner's Manual

internal battery

- Built-in LED indicates when battery level is 100% or below 5%

Specifications

OVERVIEW	
UPC Code	037332189363
Product Type	Portable Charger
Charging Form Factor	Portable
Device Compatibility	Phone; Tablet; Amazon Kindle
Country/Region	Global
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	USB-C (FEMALE)
Input Plug Type Details	USB-A to USB-C cable provided
OUTPUT	
Output Capacity (Watts)	5
Continuous Output Capacity (Watts)	5
Overload Protection	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	No
Capacity (Ah)	2.6
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	USB 3.0 MICRO-B (FEMALE)
CHARGING	
Number of Charging Ports	1
Total Charging Amps	1A
Total Charging Watts	5
Charging Method	USB



Powering Business Worldwide



Charging Method Detail	2,600 mAh
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(1) 1A
Magnetic Charging	No
Wireless Charging	No
Compatible Devices	Portable Speaker; Smartphone; Tablet
PHYSICAL	
Color	Black
Total Number of Ports	2
Shipping Dimensions (hwd / in.)	1.80 x 5.30 x 5.90
Shipping Dimensions (hwd / cm)	4.57 x 13.46 x 14.99
Shipping Weight (lbs.)	0.41
Shipping Weight (kg)	0.19
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	2.1 x 3.0 x 9.0
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Quick Charge Compliant	No
Number of USB Hub Ports	0
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.