

Low-profile power center designed for flat-panel TVs, rear-screen projection System and more - Isobar Audio/Video Power Center

MODEL NUMBER: HT2210ISOCTR



Description

Tripp Lite's HT2210ISOCTR Isobar Audio/Video Power Center provides ultimate protection - 5100 joules - stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for flat-panel TVs, rear-screen projection systems and more. Premium Isobar surge protection technology. Low-profile design that fits neatly behind flat panel TV's. HD 2.2 GHz (gold) coaxial protects against surges from coming in on the coax input. Ethernet protection with RJ45 protects from surges coming in on the network. All-metal housing, 2 AC outlets, 3 diagnostic LEDs, 10-ft and 18-in. detachable cords with right-angle plugs, 24K gold plug contacts, circuit breaker, fail-safe thermal fusing and audible alarm. Remote AC/DC control jack allows remote on/off control from an external component. Includes mounting brackets. \$100,000 Ultimate Lifetime Insurance coverage (USA/Canada only).

Features

- 5100 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- Rugged all-metal housing safely withstands the strongest surges
- 2 surge/spike protected NEMA 5-15R AC outlets
- 10-ft. and 18-in. detachable cords with right-angle NEMA 5-15P plugs enable convenient placement anywhere within a home/business theater system.
- 1-line HD2.2 GHz (gold) coaxial surge protection
- 1-Network/Ethernet protection with RJ45
- 3 diagnostic LEDs (LINE OK, GROUND OK & SURGE OK)
- Included brackets enable convenient mounting behind any flat-panel TV
- Illuminated master switch provides one-touch power control over all components
- Circuit breaker protects against dangerous system overload
- TUV tested to UL standards 1449 and 962A
- Fail-safe thermal fusing acts like an additional circuit breaker, shutting down the unit and connected equipment during a catastrophic surge
- Audible alarm immediately alerts you to damaged protection circuitry, perfect for when LEDs aren't normally viewed
- 24k gold plug contacts resist corrosion to improve AC power flow

Highlights

- 2 surge/spike protected AC outlets
- 5100 joules surge suppression rating
- 1-line HD 2.2 GHz (gold) coaxial surge protection
- 1-Network/Ethernet protection with RJ45
- 3 Diagnostic LEDs
- 10 ft. and 18 in. detachable power cords with right-angle plugs
- All-metal housing

Package Includes

- HT2210ISOCTR Audio/Video Power Center
- Mounting brackets
- Instruction manual with warranty information
- 1 Coax Cable
- 1 RJ45 Network Cable



Powering Business Worldwide



- Remote AC/DC control jack permits remote on/off control from an external component
- \$100,000 Ultimate Lifetime Insurance (USA/Canada only) covers connected components against surge damage—for life!

Specifications

OVERVIEW	
UPC Code	037332136183
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	255000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	12
Overload Protection	12-amp circuit breaker
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	On/Off power switch and circuit breaker switch
Audible Alarm	Audible alarm
Diagnostic LED Details	3
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	5100
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Safe Thermal Fusing	Yes



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line (2.2 GHz Bandwidth)
Network (Ethernet) Protection	Yes
Telephone/DSL Protection	No
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Black
Included Mounting Accessories	Mounting brackets
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	220.49mm
Outlets Measurement (Center to Center)	45mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.50 x 10.25 x 10.00
Shipping Dimensions (hwd / cm)	6.35 x 26.04 x 25.40
Shipping Weight (lbs.)	3.75
Shipping Weight (kg)	1.70
Unit Dimensions (hwd / in.)	1.500 x 4.500 x 9.250
Unit Weight (lbs.)	2.6
Unit Weight (kg)	1.18
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.