



Powering Business Worldwide

7-Outlet Home/Business Theater Surge Protector, 6-ft. Cord, 1500 Joules, Coaxial Protection

MODEL NUMBER: HT706TV



Highlights

- 7 outlets / 6 ft. cord
- 1500 joule rating
- 2.2 GHz gold coaxial surge protection

Package Includes

- HT706TV Home/Business Theater Surge Suppressor
- 6 ft. gold coaxial cable
- Instruction manual with warranty information

Description

Tripp Lite's HT706TV Home/Business Theater Surge Suppressor provides high-performance protection (1500 joules) stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 7 outlets (with transformer spacing) and 1-line 2.2GHz gold coaxial protection safeguard an entire home/business theater system. \$50,000 Ultimate Lifetime Insurance coverage (U.S., Canada, and Puerto Rico only). Includes two diagnostic LEDs, 6 ft. cord with a right-angle plug and 6 ft. coaxial cable.

Features

- 1500 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected components against surge damage...for life!
- 7 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely-spaced outlets accommodate up to 4 transformers
- 1 set of 2.2 GHz gold coaxial connectors (with included 6 ft. gold coaxial cable) safeguard components on cable, satellite or antenna line
- 6 ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection and grounding status
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Integrated circuit breaker protects against dangerous system overload
- High-impact plastic housing (black) stands up to the most demanding environments
- UL and CSA listed
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing



Powering Business Worldwide

equipment damage and indicating replacement is required

Specifications

| OVERVIEW | |
|------------------------------------|--|
| UPC Code | 037332121493 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Cord Gauge Type | 14 gauge; SJT |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 60000 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 6 |
| Right-Angle Plug | Yes |
| Input Cord Length (m) | 1.83 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (7) 5-15R |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | (4) Yes |
| Right-Angle Outlets | Yes |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | Yes |
| Switches | Combination AC circuit breaker and 2 position red illuminated on/off power switch |
| Diagnostic LED Details | Built-in LEDs confirm protection and grounding status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 1500 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| UL1449 Let Through Rating | 400 L-N, 400 L-G, 500 N-G |
| EMI / RFI Filtering | Up to 40 dB |
| Automatic Shut-Off | Yes |



Powering Business Worldwide

| DATALINE SURGE SUPPRESSION | |
|--|---|
| Cable (Coax) Protection | Yes |
| Cable (Coax) Protection Details | 1 line |
| Network (Ethernet) Protection | No |
| Telephone/DSL Protection | No |
| PHYSICAL | |
| Color | Black |
| Material of Construction | Plastic |
| Power Cord Color | Black |
| Housing Color | Black |
| Mounting Holes or Slots | Yes |
| Slot or Hole Mount Measurement (Center to Center) | 160mm |
| Outlets Measurement (Center to Center) | Distance between transformer outlet and standard outlet = 38.10mm; Distance between standard outlets = 25.40mm |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / in.) | 14.10 x 1.75 x 5.90 |
| Shipping Dimensions (hwd / cm) | 35.81 x 4.44 x 14.99 |
| Shipping Weight (lbs.) | 1.90 |
| Shipping Weight (kg) | 0.86 |
| Unit Dimensions (hwd / in.) | 1.500 x 14.000 x 3.250 |
| Unit Dimensions (hwd / cm) | 3.8 x 35.6 x 7 |
| Unit Weight (lbs.) | 1 |
| Unit Weight (kg) | 0.45 |
| FEATURES & SPECIFICATIONS | |
| Rotatable Outlets | No |
| Antimicrobial | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 Ultimate Lifetime Insurance |



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.