

SmartRack 1U Hinged Wall-Mount Patch Panel Bracket

MODEL NUMBER: **N060-001**



Mounts a patch panel or network switch to a wall, while providing easy access to rear cabling. A dependable alternative to full-size rack installation recommended for server rooms.

Description

The N060-001 1U Hinged Wall-Mount Patch Panel Bracket allows you to mount a 1U patch panel or network switch to a wall instead of investing in a full-size rack. Precision-made from heavy-duty 14-gauge steel with a glossy black finish, this bracket supports universal left- or right-hinge mounting that accepts standard 19-inch patch panels. Two keyhole slots are spaced 16 inches apart to align with wall studs to ensure secure wall-mounting. The rear cutout lets you feed cable through a wall opening to streamline installations and reduce cable clutter. Smooth laser-cut edges protect cable jackets from damage and wear. Stamped horizontal reinforcement ribs on the back of the bracket keep mounted equipment stable and secure.

Features

Dependable Alternative to Expensive Rack-Mounting

- Mounts a 1U patch panel or network switch to a wall
- Supports universal left- or right-hinge mounting
- Compatible with standard 19 in. patch panels

Built for Stability

- Keyhole mounting slots spaced 16 in. apart to align with wall studs
- Stamped horizontal reinforcement ribs on rear keep mounted equipment secure

Convenient Rear Cutout

- Allows cable to be fed through wall openings
- Streamlines installations and reduces cable clutter

Precision-Made with Laser-Cut Metal

- Heavy-duty 14ga steel construction with glossy black finish
- Smooth laser-cut edges protect cables from damage and wear

Highlights

- Precision-made from heavy-duty 14ga steel with black finish
- Supports universal left- or right-hinge mounting
- Keyhole mounting slots spaced 16 in. apart to align with wall studs
- Rear cutout for through-the-wall cabling
- Compatible with standard 19 in. patch panels

Package Includes

- N060-001 1U Hinged Wall-Mount Patch Panel Bracket
- (4) Mounting screws



Powering Business Worldwide



Specifications

| OVERVIEW | |
|-------------------------------------|---------------------------|
| UPC Code | 037332197887 |
| Accessory Type | Mounting Bracket |
| Technology | Cat5/5e; Cat6; Cat6a |
| Accessory Class | Rack Accessories |
| PHYSICAL | |
| Color | Black |
| Rack Height | 1U |
| Maximum Device Depth (cm) | 13.97 |
| Maximum Device Depth (in.) | 5.5 |
| Maximum Device Depth (mm) | 140 |
| Shipping Dimensions (hwd / in.) | 2.40 x 6.40 x 21.10 |
| Shipping Dimensions (hwd / cm) | 6.10 x 16.26 x 53.59 |
| Shipping Weight (lbs.) | 1.60 |
| Shipping Weight (kg) | 0.73 |
| Unit Dimensions (hwd / in.) | 5.827 x 19.370 x 1.252 |
| Unit Dimensions (hwd / cm) | 14.8 x 49.2 x 3.18 |
| Unit Weight (lbs.) | 1.25 |
| Unit Weight (kg) | 0.57 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.