

Cat5e/6 Shielded Surface-Mount Junction Box, 110 IDC, TAA

MODEL NUMBER: N237-001-SH



Fast, easy, cost-effective way to directly connect 2 Cat5e/6 cables without using couplers or connectors. Ideal for audio/video, voice and Ethernet applications.

Description

The N237-001-SH Cat5e/6 Shielded Surface-Mount Junction Box is a fast, easy, cost-effective method of directly connecting two Cat5e/6 cables without using couplers or connectors. Designed for completing audio/video, voice and Ethernet applications, this junction box comes with screws and double-sided adhesive tape for quick mounting, as well as cable ties for keeping the cables neat and secure. It's made from ABS UL 94V-0 plastic and is recommended for use with solid conductor cable. The UL-listed box is color-coded for 568A/B wiring for easy 110 punchdown termination. The shielded N237-001-SH protects the signal against EMI/RFI line noise and has a dedicated space on the punchdown block for grounding.

Features

Completes A/V, Voice and Ethernet Applications

- Directly connects 2 Cat5e/6 cables without couplers or connectors
- Uses standard 110 punchdown termination
- Recommended for use with solid conductor cable
- Protects against EMI/RFI line noise
- Dedicated space on punchdown block for grounding
- Color-coded for 568A/B wiring
- Mounting hardware and cable ties included
- Durable ABS UL 94V-0 plastic housing

TAA-Compliant

- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Uses standard 110 punchdown termination
- Recommended for use with solid conductor cable
- Color-coded for 568A/B wiring
- Protects against EMI/RFI line noise
- Dedicated space on punchdown block for grounding

Package Includes

- N237-001-SH Cat5e/6 Shielded Surface-Mount Junction Box
- Mounting hardware
- (2) Nylon cable ties

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332197320 |



Powering Business Worldwide



| | |
|--------------------------------------|----------------------------|
| Technology | Cat5/5e; Cat6 |
| Country/Region | Global |
| CONNECTIONS | |
| Side A - Connector 1 | 110 IDC |
| Side B - Connector 1 | 110 IDC |
| PHYSICAL | |
| Color | Silver |
| Total Number of Ports | 0 |
| Shipping Dimensions (hwd / in.) | 0.25 x 4.90 x 4.09 |
| Shipping Dimensions (hwd / cm) | 0.64 x 12.45 x 10.39 |
| Shipping Weight (lbs.) | 0.06 |
| Shipping Weight (kg) | 0.03 |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.