

24-Port 1U Rack-Mount 110-Type Color-Coded Patch Panel, RJ45 Ethernet, 568B, Cat6

MODEL NUMBER: N253-024-RBGY



Manages and organizes up to 24 input and output Cat6 network cable connections in just 1U of an EIA-standard 19 in. rack. Recommended for Ethernet, Fast Ethernet and Gigabit Ethernet network applications.

Description

The UL-approved N253-024-RBGY 24-Port 1U Rack-Mount 110-Type Color-Coded Patch Panel manages and organizes up to 24 input and output UTP Cat6 network cable connections in just 1U of an EIA-standard 19 in. rack.

The 24 RJ45 ports are split into four banks of six ports each that are color-coded—red, blue, green and yellow—for easily identifiable zones. Rear 110 connections are also color-coded for convenient EIA/TIA 568A/B wiring. All ports are numbered front and rear for quick identification of connections.

Recommended for Ethernet, Fast Ethernet and Gigabit Ethernet network applications, this durable metal patch panel supports 22 to 26 AWG stranded and solid wire.

Features

Manages and Organizes 24 UTP Cat6 Network Connections

- Recommended for Ethernet, Fast Ethernet and Gigabit Ethernet network applications
- Ports split into 4 color-coded banks of 6 ports each for convenient zone cabling
- Color-coded 110 connections for EIA/TIA 568A/B wiring
- Ports numbered front and rear for easy ID of cable runs
- Supports 22 to 26 AWG stranded and solid wire

Reliable Construction and Easy Installation

- Mounts easily into 1U of EIA-standard 19 in. rack
- UL-approved and RoHS-compliant
- Durable metal construction
- Meets or exceeds EIA/TIA TSB-40 Cat6 connecting hardware specifications

Highlights

- 4 color-coded banks for convenient zone cabling
- Color-coded rear 110 connections for EIA/TIA 568A/B wiring
- Supports 22 to 26 AWG stranded and solid wire
- Ports numbered front and rear for easy ID of cable runs
- Mounts into 1U of EIA-standard 19 in. rack

Package Includes

- N253-024-RBGY 24-Port 1U Rack-Mount 110-Type Color-Coded Patch Panel
- Mounting hardware
- Quick Start Guide

Specifications

OVERVIEW



Powering Business Worldwide



UPC Code	037332197450
Product Type	Punchdown
Technology	Cat6
CONNECTIONS	
Number of Ports	24
Side A - Connector 1	(24) 110 IDC
Side B - Connector 1	(24) RJ45 (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	3.90 x 2.90 x 21.90
Shipping Dimensions (hwd / cm)	9.91 x 7.37 x 55.63
Shipping Weight (lbs.)	1.40
Shipping Weight (kg)	0.64
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.