

# PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 2 ft. (0.61 m), Green

MODEL NUMBER: P004-002-AGN



Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 2 ft.

## Features

**C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment** This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 2-ft. (0.61 m). The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

**Color-Coded to Avoid Misidentification That Can Cause Costly Downtime** This computer power extension cord features a green SJT jacket and fully molded green ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

## Specifications

OVERVIEW	
UPC Code	037332198778
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14

## Highlights

- Recommended for powering computers, printers and other essential peripherals
- Adds 2-ft. (0.61 m) to your existing connection to provide more flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable
- Color-coded green for fast, easy identification in a crowded rack or workstation

## Applications

- Connect devices like computers, servers and monitors to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

## Package Includes

- P004-002-AGN C14 Male to C13 Female Power Cable, 2-ft. (0.61 m), Green



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	IEC-320-C13
<b>PHYSICAL</b>	
Plug Color	Green
Cable Jacket Color	Green
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	2
Cable Length (m)	0.61
Cable Length (cm)	60.96
Shipping Dimensions (hwd / in.)	0.50 x 9.30 x 6.30
Shipping Dimensions (hwd / cm)	1.27 x 23.62 x 16.00
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.