

## Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 3 ft. (0.91 m), Red

MODEL NUMBER: P018-003-ARD



Connects a PDU or UPS system with a C14 input port to network hardware, such as computers, servers and storage drives, with C15 power connectors.

### Features

#### Safe, Reliable Power Solution

- Connects PDU or UPS system with C14 input to network hardware with C15 power connectors
- Ideal for replacing an old or lost cord
- Recommended for Cisco, HP and other C15-compatible hardware

#### Color-Coded Cable and Connectors

- Colored red for easy identification in crowded rack or workstation

#### Optimum Construction

- 14 AWG wire
- Flexible SJT jacket
- 250V/15A rating
- UL-listed

## Specifications

| OVERVIEW             |                          |
|----------------------|--------------------------|
| UPC Code             | 037332199133             |
| Device Compatibility | Network Switch; UPS; PDU |
| Country/Region       | North America            |
| INPUT                |                          |

### Highlights

- Easy-to-identify red SJT jacket and fully molded red ends
- Flexible 14 AWG wire for easy routing
- 250V/15A rating
- UL-listed
- Recommended for Cisco®, HP and other C15-compatible hardware

### Package Includes

- P018-003-ARD Heavy-Duty Computer Power Cord, Red, 3 ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                             |
|--------------------------------------|-----------------------------|
| Maximum Input Amps                   | 15                          |
| Voltage Compatibility (VAC)          | 100-250                     |
| <b>CONNECTIONS</b>                   |                             |
| Side A - Connector 1                 | IEC-320-C14                 |
| Side B - Connector 1                 | IEC-320-C15                 |
| <b>PHYSICAL</b>                      |                             |
| Plug Color                           | Red                         |
| Cable Jacket Color                   | Red                         |
| Cable Jacket Material                | PVC                         |
| Cable Jacket Rating                  | VW-1                        |
| Power Cord Jacket Type               | SJT                         |
| Cable Outer Diameter (OD)            | 9.3mm                       |
| Number of Conductors                 | 3                           |
| Wire Gauge (AWG)                     | 14                          |
| Wire Gauge (OD - mm <sup>2</sup> )   | 2.08                        |
| Cable Length (ft.)                   | 3                           |
| Cable Length (m)                     | 0.91                        |
| Cable Length (cm)                    | 91.44                       |
| Shipping Dimensions (hwd / in.)      | 9.90 x 7.00 x 0.50          |
| Shipping Dimensions (hwd / cm)       | 25.15 x 17.78 x 1.27        |
| Shipping Weight (lbs.)               | 0.44                        |
| Shipping Weight (kg)                 | 0.20                        |
| <b>ENVIRONMENTAL</b>                 |                             |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range             | 10% to 65% RH               |
| Storage Humidity Range               | 10% to 65% RH               |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                             |
| Antibacterial                        | No                          |
| Angled Plug                          | No                          |
| High Voltage                         | Yes                         |
| Locking Plug                         | No                          |
| Coiled Power Cord                    | No                          |



Powering Business Worldwide

TRIPP LITE  
SERIES

| STANDARDS & COMPLIANCE              |                           |
|-------------------------------------|---------------------------|
| Product Certifications              | cUL Listed; UL Listed     |
| Product Compliance                  | RoHS                      |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.