

4K HDMI Audio De-Embedder/Extractor with TOSLINK and 3.5 mm Stereo Output, 5.1 Channel, HDCP, 4K 30Hz, 6-in. (15.24 cm)

MODEL NUMBER: P130-06N-AUDIO



Separates the audio track from an HDMI audio/video signal and sends it to a stereo receiver, speakers or other separate audio system. Ideal for connecting a Blu-ray player or other HDMI source to speakers with no HDMI input.

Features

Extracts Audio from an HDMI Signal and Sends It to a Separate Audio System

- Recommended for connecting HDMI source to speakers that don't have HDMI input
- 3.5 mm stereo and TOSLINK optical outputs connect to analog or digital non-HDMI audio equipment
- LED indicates the unit is receiving power or transmitting an audio/video signal
- Built-in 6 in. HDMI cable connects to audio/video source
- Included 3 ft. USB Micro-B cable provides power to the unit

Versatile Audio Options

- Supports 2-channel stereo and multi-channel audio up to 5.1 surround sound
- Supports uncompressed, such as LPCM, and compressed audio, including DTS and Dolby Digital

Vibrant UHD Video

- Transmits UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Supports 24-bit True Color (8 bits per channel) at 4K x 2K
- Supports 36-bit Deep Color (12 bits per channel) at 1080p
- Supports optional 3D formats up to 300 MHz
- Complies with HDCP 1.4 standards

Specifications

OVERVIEW

Highlights

- Built-in 6 in. HDMI cable connects to audio/video source
- Supports multi-channel audio up to 5.1 surround sound
- Features 3.5 mm stereo and TOSLINK optical audio outputs
- Transmits UHD video resolutions up to 3840 x 2160 (4K x 2K)
- Powered via USB Micro-B connection

Package Includes

- P130-06N-AUDIO UHD 4K x 2K HDMI Audio De-Embedder/Extractor
- USB Micro-B cable, 3 ft.
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332200921
Technology	HDMI; Stereo Audio; Toslink/SPDIF
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	TOSLINK (MALE)
Side B - Connector 3	3.5MM (FEMALE)
Side B - Connector 4	MICRO-USB B (FEMALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Dimensions (hwd / cm)	2.31 x 14.00 x 10.01
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.