

Mini DisplayPort Extension Cable, 4K @ 60 Hz, HDCP 2.2 (M/F), 10 ft. (3.05 m)

MODEL NUMBER: P585-010



Extends your existing Mini DisplayPort (mDP) connection by 10 ft.

Description

The P585-010 Mini DisplayPort Extension Cable (M/F) attaches to your current mDP cable to extend it by 10-ft. (3.05 m). It supports Ultra High Definition video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, allowing you to stream digital video and audio to an mDP display from an mDP computer, such as a MacBook® or Surface® Book, or tablet, including Microsoft's Surface Pro 4. The P585-010 connects to any computer, laptop, mobile device or display that features an mDP, Thunderbolt or Thunderbolt 2 port. Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Molded nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. A flexible PVC jacket protects twisted 32 AWG data lines and 32 AWG power lines.

Features

Extends an Existing Mini DisplayPort Cable an Extra 10-ft. (3.05 m)

- Female connector attaches to current mDP cable to add length
- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports DisplayPort v1.2a and HDCP 2.2
- Recommended for devices with mDP, Thunderbolt or Thunderbolt 2 ports

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors and gold-plated contacts for optimal signal quality
- Integral strain relief for long life
- Twisted 32/32 AWG data/power lines
- Flexible PVC jacket and small footprint for easy installation in tight spaces

Specifications

OVERVIEW

Highlights

- Supports video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Premium foil and braid shielding
- Molded nickel-plated connectors and gold-plated contacts
- Supports DisplayPort™ v1.2a and HDCP 2.2
- Connects to mDP, Thunderbolt™ or Thunderbolt 2 port

Package Includes

- P585-010 Mini DisplayPort Extension Cable (M/F), 10-ft. (3.05 m)



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332201652
Product Type	Passive Cable
Technology	DisplayPort
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	MINI DISPLAYPORT (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Cable Length (cm)	304.80
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.