



Protect It! 6-Outlet Low-Profile Surge Protector, Direct Plug-In, 750 Joules, Diagnostic LED

MODEL NUMBER: SK6-0











Highlights

- 6 outlets/direct plug-in
- 750 joule rating

Package Includes

- SK6-0 Surge Suppressor
- · Warranty information
- Instruction manual

Description

The SK6-0 Surge Suppressor is ideal for protecting audio/video devices and printers. This direct plug-in surge suppressor features six outlets and 750 joules of surge energy absorption.

Features

- 6 outlets; direct plug-in
- Surge energy absorption: 750 joules; 27,000 amps
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

| OVERVIEW | | |
|------------------------------------|-----------------|--|
| UPC Code | 037332010261 | |
| | | |
| INPUT | | |
| Nominal Input Voltage(s) Supported | 120V AC | |
| Recommended Electrical Service | 120V (110-125V) | |
| Input Cord Length Details | Direct Plug-In | |
| Voltage Compatibility (VAC) | 120 | |
| Maximum Surge Amps | 36000 | |
| Input Plug Type | NEMA 5-15P | |
| Input Cord Length (ft.) | 0 | |
| Right-Angle Plug | No | |





| Input Cord Length (m) | 0.00 | |
|--|--|--|
| Integrated Cord Clip | No | |
| OUTPUT | | |
| Frequency Compatibility | 50 / 60 Hz | |
| Output Receptacles | (6) 5-15R | |
| Circuit Breaker (amps) | 15 | |
| Transformer Accommodation | (2) Yes | |
| Right-Angle Outlets | No | |
| USER INTERFACE, ALERTS & CONTROLS | | |
| Diagnostic LED(s) | Yes | |
| | | |
| SURGE / NOISE SUPPRESSION | | |
| AC Suppression Joule Rating | 750 | |
| AC Suppression Response Time | <1 ns | |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression | |
| AC Suppression Surge Current Rating | 27,000 amps | |
| UL1449 Let Through Rating | 400, 500, 500 | |
| Immunity | Conforms to IEE 587 / ANSI C62.41 | |
| Automatic Shut-Off | Yes | |
| DATALINE SURGE SUPPRESSION | | |
| Cable (Coax) Protection | No | |
| Network (Ethernet) Protection | No | |
| Telephone/DSL Protection | No | |
| PHYSICAL | | |
| Material of Construction | Plastic | |
| Housing Color | Light Gray | |
| Mounting Holes or Slots | No | |
| Outlets Measurement (Center to Center) | Distance between horizontal outlets = 25.2mm; Distance between vertical outlets = 39mm | |
| Receptacle Color | Gray | |
| Shipping Dimensions (hwd / in.) | 6.30 x 8.70 x 1.50 | |
| Shipping Dimensions (hwd / cm) | 16.00 x 22.10 x 3.81 | |
| Shipping Weight (lbs.) | 0.61 | |
| Shipping Weight (kg) | 0.28 | |





| Unit Dimensions (hwd / in.) | 4.800 x 4.350 x 1.420 | |
|--|---|--|
| Unit Dimensions (hwd / cm) | 12.19 x 11.05 x 3.6 | |
| Unit Weight (lbs.) | .406 | |
| Unit Weight (kg) | 0.18 | |
| FEATURES & SPECIFICATIONS | | |
| Rotatable Outlets | No | |
| Antimicrobial | No | |
| STANDARDS & COMPLIANCE | | |
| Product Certifications | cUL Listed; UL 1449; UL Listed | |
| Product Compliance | RoHS | |
| WARRANTY & SUPPORT | | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty | |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$10,000 Ultimate Lifetime Insurance | |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.