



6-Outlet Surge Protector, Direct Plug-In, 750 Joules, Diagnostic LED, Black

MODEL NUMBER: SK6-0B



Highlights

- 6 outlets/direct plug-in
- 750 joule rating

Package Includes

- SK6-0B Surge Suppressor
- Warranty information
- Instruction manual

Description

The SK6-0B Surge Suppressor is ideal for protecting audio/video devices and printers. This direct plug-in surge suppressor features 6 outlets and 750 joules of surge energy absorption. \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 6 outlets: direct plug-in
- Surge energy absorption: 750 joules
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
 equipment damage and indicating replacement is required

Specifications

OVERVIEW		
UPC Code	037332146397	
Charging Form Factor	Direct Plug-In	
Product Type	Surge Protector	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V	
Input Cord Length Details	Direct Plug-In	
Voltage Compatibility (VAC)	120	





Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CON	ITROLS
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green - Protected; Red - Grounded
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	750
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 500, 500
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Housing Color	Black
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 25.2mm; Distance between vertical outlets = 39mm





Receptacle Color	Black
Shipping Dimensions (hwd / in.)	6.30 x 8.70 x 1.50
Shipping Dimensions (hwd / cm)	16.00 x 22.10 x 3.81
Shipping Weight (lbs.)	0.61
Shipping Weight (kg)	0.28
Unit Dimensions (hwd / in.)	3.700 x 5.000 x 1.200
Unit Dimensions (hwd / cm)	1.45 x 1.97 x .47
Unit Weight (Ibs.)	2.65
Unit Weight (kg)	1.20
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.