



Protect It! 230V 6-Universal Outlet Surge Protector, 1.8M Cord, British Plug, 750 Joules

MODEL NUMBER: SUPER60MNIB











Highlights

- 6 universal outlets
- 1.8 m power cord with British plug
- 750 joule rating
- Lighted on/off switch with integrated circuit breaker

Package Includes

- SUPER6OMNI B AC surge suppressor
- Instruction manual and warranty information

Description

The Protect It!® SUPER6OMNI B offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER6OMNI B offers six universal outlets and a 1.8-meter AC line cord with a British plug. AC suppression rated at 750 joules shields equipment from surges and line noise. Internal shutters also offer additional protection. Lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Right-angle outlets keep connected cords from blocking adjacent outlets. Attractive light gray high-impact housing.

Features

- Protect It!™ SUPER6OMNI B offers economical AC surge suppression
- 750 joules AC surge suppression shields equipment from surges and line noise
- 6 universal outlets protect computers and peripherals
- · Internal shutters provide additional safety
- 1.8 m AC line cord with British plug
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- · Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- Right-angle outlets keep connected cords from blocking adjacent outlets

Specifications

OVERVIEW	
UPC Code	037332121158
INPUT	





Nominal Input Voltage(s) Supported	230V AC	
Recommended Electrical Service	230V (220-250V)	
Voltage Compatibility (VAC)	220-250	
Maximum Surge Amps	13500	
Input Plug Type	British	
Input Cord Details	VDE H05VV-F 1.0mm2	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(6) Universal outlets	
Circuit Breaker (amps)	10	
Overload Protection	10A resettable illuminated combo switch/circuit breaker	
Outlet Orientation	right-angled	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	No	
Switches	Two position power switch	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	750	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction	Plastic	
Power Cord Color	Black	
Housing Color	Light Gray	





Yes		
219.5 mm		
51mm		
Gray		
2.10 x 4.40 x 16.80		
5.33 x 11.18 x 42.67		
1.40		
0.64		
1.750 x 16.000 x 2.500		
39.4 x 6.4 x 3.2		
1.0		
0.45		
FEATURES & SPECIFICATIONS		
No		
No		
STANDARDS & COMPLIANCE		
RoHS		
WARRANTY & SUPPORT		
Lifetime limited warranty		

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.