



## Protect It! 230V 6-Universal Outlet Surge Protector, 1.8M Cord, German/French Plug, 750 Joules

## MODEL NUMBER: SUPER60MNID











### **Highlights**

- 6 universal outlets
- 1.8 m power cord with German/French plug
- 750 joule rating
- Lighted on/off switch with integrated circuit breaker

#### **Package Includes**

- SUPER6OMNI D AC surge suppressor
- Instruction manual and warranty information

## Description

The Protect It!® SUPER6OMNI D offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER6OMNI D offers six universal outlets and a 1.8-meter AC line cord with German/French plug. Internal shutters offer additional safety. AC suppression rated at 750 joules shields equipment from surges and line noise. Lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Right-angle outlets keep connected cords from blocking adjacent outlets. Attractive light gray high-impact housing.

#### **Features**

- Protect It!™ SUPER6OMNI D offers economical AC surge suppression
- 750 joules AC surge suppression shields equipment from surges and line noise
- 6 universal outlets protect computers and peripherals
- 1.8 m AC line cord with German/French plug
- · Internal shutters provide additional safety
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- · Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- · Right-angle outlets keep connected cords from blocking adjacent outlets

# **Specifications**

OVERVIEW	
UPC Code	037332121141





INPUT		
Nominal Input Voltage(s) Supported	230V AC	
Recommended Electrical Service	230V (220-250V)	
Voltage Compatibility (VAC)	220-250	
Maximum Surge Amps	13500	
Input Plug Type	German; French	
Input Cord Details	VDE H05VV-F 1.0mm2	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(6) Universal outlets	
Circuit Breaker (amps)	10	
Overload Protection	10A resettable illuminated combo switch/circuit breaker	
Outlet Orientation	right-angled	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	No	
Switches	Two position power switch	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	750	
AC Suppression Response Time	<1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction	Plastic	
Power Cord Color	Black	





Housing Color	Light Gray	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	219.5 mm	
Outlets Measurement (Center to Center)	51mm	
Receptacle Color	Gray	
Shipping Dimensions (hwd / in.)	17.20 x 2.00 x 4.60	
Shipping Dimensions (hwd / cm)	43.69 x 5.08 x 11.68	
Shipping Weight (lbs.)	1.44	
Shipping Weight (kg)	0.65	
Unit Dimensions (hwd / in.)	1.750 x 16.000 x 2.500	
Unit Dimensions (hwd / cm)	39.4 x 6.4 x 3.2	
Unit Weight (lbs.)	1.0	
Unit Weight (kg)	0.45	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.