

# Internal Battery Pack - Compatible with select SmartOnline 20kVA, 30kVA, 40kVA 3-Phase UPS System & SUBF2030 External Battery Frame

MODEL NUMBER: SURBC2030



### Highlights

- Internal Battery Pack offers extended runtime operation for select SmartOnline 20, 30 and 40kVA 3-Phase UPS Systems & SUBF2030 External Battery Frame
- Simple installation scheme with pre-wired and assembled batteries

### Package Includes

- SURBC2030 Internal Battery Pack (set of two pre-wired battery strings)
- Instruction and installation manual

### Description

The SURBC2030 Internal Battery Pack is a set of two pre-wired strings of internal batteries that are designed to be installed within the internal battery compartment for select SmartOnline® 20kVA, 30kVA and 40kVA 3-Phase UPS Systems or SUBF2030 External Battery Frame. When installed as directed, the two assembled battery strings that make up a SURBC2030 maintain a nominal battery voltage of 240V DC. The SURBC2030 also serves as a replacement for existing internal battery packs.

### Features

- Set of two pre-wired strings of internal batteries that are designed to be installed within the internal battery compartment of select SmartOnline 20, 30 and 40kVA 3-Phase UPS System or SUBF2030 External Battery Frame
- When installed as directed, the two assembled battery strings that make up a SURBC2030 maintain a nominal battery voltage of 240V DC
- Also serves as a replacement for existing internal battery packs

## Specifications

OVERVIEW	
UPC Code	037332141743
Accessory Type	Internal Battery Pack
INPUT	
Input Phase	3-Phase
BATTERY	
DC System Voltage (VDC)	240



Powering Business Worldwide



UPS Connection	Included cabling
<b>PHYSICAL</b>	
External Battery Pack Form Factor	Tower
Shipping Dimensions (hwd / in.)	18.00 x 20.00 x 31.00
Shipping Dimensions (hwd / cm)	45.72 x 50.80 x 78.74
Shipping Weight (lbs.)	168.00
Shipping Weight (kg)	76.20
Unit Dimensions (hwd / in.)	7.992 x 5.984 x 27.008
Unit Dimensions (hwd / cm)	- 20,3 x 15,2 x 68,6
Unit Weight (lbs.)	123.00
Unit Weight (kg)	55.79
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.