

Protect It! 230V Surge Protector with 2 Schuko Type F Outlets, 0.33M Cord, 380 Joules, German plug

MODEL NUMBER: TLP2USBD



Highlights

- 2 safety outlets
- 380 joule rating
- 2 USB ports
- 33 cm cord

Package Includes

- TLP2USBD surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP2USBD offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP2USBD offers 2 Schuko type F outlets and 33 cm AC line cord. Two USB ports are perfect for charging cell phones, iPods, MP3 players and other mobile devices. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP2USBD offers economical AC surge suppression
- 380 joules AC surge suppression shields equipment from surges and line noise
- 2 Schuko outlets protects computers and peripherals
- 2 USB ports are perfect for changing cell phones, iPods, MP3 players and other mobile devices
- 33 cm cord with German plug
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145376
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	German



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Input Cord Length (ft.)	1
Right-Angle Plug	Yes
Input Cord Length (m)	0.30
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(2) Schuko Type F
Circuit Breaker (amps)	10
Transformer Accommodation	(1) Yes
CONNECTIONS	
Number of Ports	2
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
CHARGING	
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	380
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Black
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	8.67 x 6.10 x 3.15
Shipping Dimensions (hwd / cm)	22.02 x 15.49 x 8.00
Shipping Weight (lbs.)	0.50

Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	5.900 x 2.165 x 1.634
Unit Dimensions (hwd / cm)	14.99 x 5.51 x 4.14
Unit Weight (lbs.)	.48
Unit Weight (kg)	0.22
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.