



# Protect It! 230V Surge Protector with 5Schuko Type F Outlets, 1M Cord, 280 Joules, German plug, Diagnostic LED

MODEL NUMBER: TLP51D



### **Highlights**

- 5 safety outlets
- 1 m cord
- "Protected" LED
- 280 joule rating

#### **Package Includes**

- TLP51D surge suppressor
- Instruction manual and product warranty information

#### **Description**

Tripp Lite's Protect It!<sup>TM</sup> TLP51D offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP51D offers 5 Schuko Type F outlets and a 1 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

#### **Features**

- Protect It!™ TLP51D offers economical AC surge suppression
- 280 joules AC surge suppression shields equipment from surges and line noise
- 5 Schucko outlets protect computers and peripherals
- 1 m cord with German plug
- "Protected" LED
- Internal safety covers protect against accidental contact with unused outlets

## **Specifications**

OVERVIEW		
UPC Code	037332145338	
INPUT		
Nominal Input Voltage(s) Supported	230V AC	
Recommended Electrical Service	230V (220-250V)	
Voltage Compatibility (VAC)	220-250	
Input Plug Type	German	
Input Cord Length (ft.)	3	





Right-Angle Plug	Yes	
Input Cord Length (m)	0.91	
Integrated Cord Clip	No	
ОИТРИТ		
Output Receptacles	(5) Schuko Type F	
Circuit Breaker (amps)	10	
Transformer Accommodation	(3) Yes	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	Yes	
Diagnostic LED Details	Protected	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	280	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Color	Light Gray	
Power Cord Color	Light Gray	
Housing Color	Light Gray	
Mounting Holes or Slots	No	
Receptacle Color	Light gray	
Shipping Dimensions (hwd / in.)	12.00 x 2.17 x 4.53	
Shipping Dimensions (hwd / cm)	30.48 x 5.51 x 11.51	
Shipping Weight (lbs.)	0.90	
Shipping Weight (kg)	0.41	
Unit Dimensions (hwd / in.)	10.430 x 1.587 x 2.000	
Unit Dimensions (hwd / cm)	26.49 x 4.01 x 5.08	
Unit Weight (lbs.)	.87	
Unit Weight (kg)	0.39	
FEATURES & SPECIFICATIONS		





Rotatable Outlets	No	
Antimicrobial	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.