

Protect It! Surge Suppressor - 6 Outlets

MODEL NUMBER: TLP606TELPP

Description

Tripp Lite's TLP606TELPP offers economical AC and phone line surge suppression for full protection of 220-240V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TLP606TELPP offers 6 total outlets, 1.8 meter cord and one diagnostic LED to warn of suppressor damage. AC suppression rated at 850 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs and 1 designated transformer plug outlet offers convenient protection of desktop computer equipment and accessories. Lifetime warranty.

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/1.8 m AC line cord

ELECTRICAL: 220-240V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 300V RMS Clamping/850 joules -Phone: Single telephone line surge suppression (RJ11 jacks, 2 wire, 1 line)

Features

- Protect It! TLP606TELPP offers economical AC and phone line surge suppression
- 850 joules AC surge suppression shields equipment from the strongest surges and line noise
- 6 AC outlets (with room for 1 transformer plug without blocking outlets) protect computers and peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes phone cable)
- 1.8 meter AC line cable
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LED confirm surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- Lifetime warranty

Highlights

- 6 outlets optimized for 220-240V Peru/Philippines use
- 1.8 m power cord
- 850 joule rating
- Diagnostic LED
- Lighted power switch

Package Includes

- TLP606TELPP AC surge suppressor
- Phone line cable
- Instruction manual and warranty information

Specifications

OVERVIEW	
UPC Code	037332098290
INPUT	
Voltage Compatibility (VAC)	220-250
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No



Powering Business Worldwide



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position power switch controls power to all outlets
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	850
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Mounting Holes or Slots	Yes
Shipping Dimensions (hwd / in.)	13.00 x 4.75 x 1.75
Shipping Dimensions (hwd / cm)	33.02 x 12.06 x 4.44
Shipping Weight (lbs.)	1.20
Shipping Weight (kg)	0.54
Unit Dimensions (hwd / in.)	10.750 x 1.750 x 1.250
Unit Dimensions (hwd / cm)	24.1 x 3.8 x 3.8
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty