



Protect It! 230V Surge Protector with 6 French/Belgian Outlets, 2M Cord, 1140 Joules, French plug

MODEL NUMBER: TLP61F



Highlights

- 6 safety outlet covers
- 2 m cord
- "Protected" LED
- 1140 joule rating

Package Includes

- TLP61F surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!TM TLP61F offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP61F offers 6 French Type E outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP61F offers economical AC surge supression
- 1140 joules AC surge suppression shields equipment from surges and line noise
- 6 French Type E outlets protects computers and peripherals
- 2 m cord with French plug
- Protected LED
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW		
UPC Code	037332145444	
INPUT		
Nominal Input Voltage(s) Supported	230V AC	
Recommended Electrical Service	230V (220-250V)	
Voltage Compatibility (VAC)	220-250	
Input Plug Type	French	
Input Cord Length (ft.)	6	





Right-Angle Plug	Yes	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Output Receptacles	(6) French/Belgian	
Circuit Breaker (amps)	10	
Transformer Accommodation	(3) Yes	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	Yes	
Diagnostic LED Details	Green Protected	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1140	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Color	Light Gray	
Power Cord Color	Light Gray	
Housing Color	Light Gray	
Mounting Holes or Slots	No	
Receptacle Color	Light gray	
Shipping Dimensions (hwd / in.)	18.20 x 1.75 x 4.80	
Shipping Dimensions (hwd / cm)	46.23 x 4.44 x 12.19	
Shipping Weight (lbs.)	1.50	
Shipping Weight (kg)	0.68	
Unit Dimensions (hwd / in.)	16.000 x 2.320 x 1.750	
Unit Dimensions (hwd / cm)	40.64 x 5.89 x 4.45	
Unit Weight (lbs.)	1.2	
Unit Weight (kg)	0.54	
FEATURES & SPECIFICATIONS		





Rotatable Outlets	No	
Antimicrobial	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.