



Protect It! 6-Outlet Surge Protector, 4-ft. Cord, 540 Joules - Accommodates 2 Transformers

MODEL NUMBER: TLP64











Highlights

- 6 outlets / 4 ft cord
- 540 joule rating
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- TLP64
- Instruction manual with warranty information

Description

Tripp Lite's TLP64 offers economical AC surge suppression for protection of workstations, desktop PCs, point-of-sale terminals and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP64 offers 6 total outlets, 4 foot cord and diagnostic LEDs to warn of suppressor damage. AC suppression rated at 540 joules shields equipment from surges and line noise. Attractive gray suppressor housing with keyhole mounting tabs offer convenient protection of desktop computer equipment and accessories. \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- · 6 outlets with integrated child safety covers
- 4ft cord
- Surge suppression rating: 540 joules
- EMI/RFI noise filtering
- Can accommodate up to 2 transformers without blocking remaining outlets
- Diagnostic LEDs indicate protection present and ground present
- Keyhole supports for wall mounting
- · Lighted power switch
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

OVERVIEW	
UPC Code	037332159694





INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	36000	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	4	
Right-Angle Plug	No	
Input Cord Length (m)	1.22	
Integrated Cord Clip	No	
оитрит		
Frequency Compatibility	60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Overload Protection	15A resettable illuminated combo switch / circuit breaker	
Transformer Accommodation	(4) Yes	
Outlet Orientation	Block style 2 rows of 3 outlets	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch	
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	540	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression	
UL1449 Let Through Rating	400v	
EMI / RFI Filtering	Up to 40 dB	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	





Telephone/DSL Protection	No	
PHYSICAL		
Color	Light Gray	
Material of Construction	Plastic	
Power Cord Color	Light Gray	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	119mm	
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5mm; Distance between standard outlet and transformer outlet = 48.5mm	
Receptacle Color	Gray	
Shipping Dimensions (hwd / in.)	11.70 x 1.75 x 7.20	
Shipping Dimensions (hwd / cm)	29.72 x 4.44 x 18.29	
Shipping Weight (lbs.)	1.40	
Shipping Weight (kg)	0.64	
Unit Dimensions (hwd / in.)	1.500 x 4.230 x 8.290	
Unit Dimensions (hwd / cm)	3.81 x 10.74 x 21.06	
Unit Weight (lbs.)	1.10	
Unit Weight (kg)	0.50	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.