

Eco-Surge 6-Outlet Surge Protector, 6-ft. cord, 2100 Joules, Remote-Controlled

MODEL NUMBER: TLP66RCG



Highlights

- Keychain remote control turns GREEN energy saving outlets on/off
- 6 outlet/6-ft cord
- 2100 joules
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- TLP66RCG ECO-SURGE Energy-Saving Surge Suppressor
- Owners Manual

Description

Tripp Lite's TLP66RCG offers reliable, GREEN surge technology that protects your computer and peripherals, the environment and your wallet. Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. Convenient, one-touch remote control turns green energy-saving outlets on and off. TLP66RCG has 6 total outlets, 6 foot cord and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 2100 joules shields equipment from surges and line noise. Attractive cool gray suppressor housing with keyhole mounting tabs and up to 4 transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals
- 433 MHz key chain remote turns GREEN outlets on/off through walls, doors and furniture from up to 75 ft. away
- 6 total AC outlets with room for 4 transformer plugs
- 4 "Remote/Power Save" GREEN outlets cut AC power to idle components when turned off via remote control - perfect for intermittent use equipment like DVD players, gaming consoles, speaker systems, monitors, printers, lighting etc.
- Two "Switched/Always-On" outlets provide continuous power for devices such as DVRs (TiVo), cable and satellite boxes, modems, routers, external hard drives, cordless phones and fax machines
- 2100 joules of AC surge suppression shields equipment from the strongest surges and line noise
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive gray suppressor housing with keyhole mounting tabs allow versatile placement options
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332158697
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	39000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Output Capacity (Watts)	1800
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status and "receiver" (red)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2100
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	400, 400, 400
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No



Powering Business Worldwide



Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Gray
Material of Construction	Plastic
Power Cord Color	Gray
Housing Color	Gray
Mounting Holes or Slots	Yes
Outlets Measurement (Center to Center)	Distance between "Remoted" outlets = 28.5mm; Distance between "Remoted" and "Switched" outlets = 50mm
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	13.00 x 2.40 x 6.50
Shipping Dimensions (hwd / cm)	33.02 x 6.10 x 16.51
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	1.670 x 4.410 x 9.250
Unit Dimensions (hwd / cm)	4.24 x 11.20 x 23.50
Unit Weight (lbs.)	1.45
Unit Weight (kg)	0.66
FEATURES & SPECIFICATIONS	
Green Energy-Saving Features	Power saving auto-shutoff ECO outlets
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.