



Protect It! 7-Outlet Surge Protector, 6 Right-Angle Outlets, 4 ft. (1.22 m) Cord, 1080 Joules, Diagnostic LED, Black Housing

MODEL NUMBER: TLP74RB











Safeguard your computer, printer, scanner, router, modem and other small home electronics against dangerous surges, spikes and line noise. Recommended for any desktop, network or home application requiring AC line protection.

Features

1080-Joule Surge Protection for Home or Office ElectronicsProtects your computer, printer, scanner, router, modem and other small home electronics against surges and spikesRecommended for any desktop, network or home electronics application requiring AC line protectionFull normal mode (H-N) and common mode (N-G/H-G) line surge suppressionFilters out disruptive EMI/RFI line noise that can cause equipment damage or data lossExceeds IEEE 587 Category A and B surge suppression specifications

7 Outlets Accept Wide Range of Electronic Devices 6 NEMA 5-15R AC outlets placed at a right angle to simplify cord managementSpecial end outlet designed for bulky transformers without blocking other outlets

Premium Safety FeaturesLighted on/off switch provides one-touch control over connected equipmentAutomatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is requiredDiagnostic LED confirms protection status at a glanceConforms to current UL 1449 3rd Edition safety standards

Fits Effortlessly Into Your Workstation4-ft. (1.22 m) AC power cord with NEMA 5-15P plug reaches nearby outletsKeyhole slots on bottom panel provide convenient wall or desk mounting optionsBlack plastic housing designed for long life

Backed by Ultimate Lifetime Insurance\$25,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332155665

Highlights

- 6 right-angle NEMA 5-15R outlets (7 total)
- 1080-joule surge protection rating
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 4 ft. AC power cord with NEMA 5-15P plug

Package Includes

- TLP74RB Protect It! 7-Outlet Surge Protector, Black Housing
- Owner's manual





INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	36000	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	4	
Right-Angle Plug	No	
Input Cord Length (m)	1.22	
Integrated Cord Clip	No	
ОИТРИТ		
Frequency Compatibility	60 Hz	
Output Receptacles	(7) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(4) Yes	
Outlet Orientation	Single row	
Right-Angle Outlets	Yes	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Combination AC circuit breaker and 2 position on/off power switch	
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1080	
AC Suppression Response Time	<1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating	400V	
EMI / RFI Filtering	Yes	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	





Network (Ethernet) Protection	No	
, ,	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction	Plastic	
Power Cord Color	Black	
Housing Color	Black	
Mounting Holes or Slots	No	
Slot or Hole Mount Measurement (Center to Center)	300 mm	
Outlets Measurement (Center to Center)	28.5mm	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	14.00 x 1.75 x 4.50	
Shipping Dimensions (hwd / cm)	35.56 x 4.44 x 11.43	
Shipping Weight (lbs.)	1.20	
Shipping Weight (kg)	0.54	
Unit Dimensions (hwd / in.)	1.330 x 2.040 x 12.400	
Unit Dimensions (hwd / cm)	3.38 x 5.18 x 31.50	
Unit Weight (lbs.)	1.04	
Unit Weight (kg)	0.47	
Input Cord Color	Black	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.