

Protect It! 230V Surge Protector with 8 French/Belgian Outlets, French Plug, 2280 Joules

MODEL NUMBER: TLP82F



Highlights

- 8 safety outlets
- 2 m power cord with French plug
- 2280 joule rating

Package Includes

- TLP82F surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP82F offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP825F offers 8 "French" Type E outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP82F offers economical AC surge suppression
- 2280 joules AC surge suppression shields equipment from surges and line noise
- 8 "French" Type E outlets protect computers and peripherals
- 2 m Cord with French plug
- Protected/Grounded LED's
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145420
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	French
Input Cord Length (ft.)	6



Powering Business Worldwide



Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) French/Belgian
Circuit Breaker (amps)	10
Transformer Accommodation	(5) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Grounded/Protected
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2280
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Black
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	14.40 x 6.50 x 2.17
Shipping Dimensions (hwd / cm)	36.58 x 16.51 x 5.51
Shipping Weight (lbs.)	1.55
Shipping Weight (kg)	0.70
Unit Dimensions (hwd / in.)	12.070 x 4.610 x 1.930
Unit Dimensions (hwd / cm)	30.66 x 11.71 x 4.90
Unit Weight (lbs.)	1.50
Unit Weight (kg)	0.68



Powering Business Worldwide



FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.