

Protect It! 230V Surge Protector with 8-Schuko Type F Outlets, German Plug, 1140 Joules, Coax/Network Protection

MODEL NUMBER: TLP82MASD



Highlights

- 8 safety outlets
- 2 m cord
- Network protection
- 1 Line coax protection
- Protected/Grounded LED's
- 1140 joule rating
- Energy saving master/subordinate outlet array

Package Includes

- TLP82MASD surge suppressor
- 1.8 aerial cable and 2 aerial adapters
- 1.8 m gold coax cable
- 1.8 m network cable
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP82MASD offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP82MASD offers 8 Schuko type F outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP82MASD offers economical AC surge suppression
- 1140 joules AC surge suppression shields equipment from surges and line noise
- 8 Shucko outlets protects computers and peripherals
- 2 m cord with German plug
- Lighted ON/OFF switch with circuit breaker
- Network Protection
- Coax Protection
- Aerial Adapters
- Energy saving master/subordinate outlet array
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145390
INPUT	
Nominal Input Voltage(s) Supported	230V AC



Powering Business Worldwide



Recommended Electrical Service	230V (220-250V)
Maximum Input Amps	10
Voltage Compatibility (VAC)	220-250
Input Plug Type	German
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(8) Schuko Type F
Circuit Breaker (amps)	10
Transformer Accommodation	(5) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Protected/Grounded
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1140
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	Yes
Telephone/DSL Protection	No
PHYSICAL	
Color	Black
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	14.80 x 7.48 x 2.17
Shipping Dimensions (hwd / cm)	37.59 x 19.00 x 5.51
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04



Powering Business Worldwide



Unit Dimensions (hwd / in.)	12.440 x 4.610 x 1.933
Unit Dimensions (hwd / cm)	31.60 x 11.71 x 4.90
Unit Weight (lbs.)	2.1
Unit Weight (kg)	0.95
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.