



# Protect It! 1-Outlet Portable Surge Protector, Direct Plug-In, 750 Joules, Tel/Modem Protection

### MODEL NUMBER: TRAVELCUBE











#### **Highlights**

- 1 AC outlet
- Direct plug-in design
- Built-in tel/modem surge protection
- 750 joule rating
- Diagnostic LED displays protection status

#### **Package Includes**

 TRAVELCUBE surge suppressor

### Description

The TRAVELCUBE is designed for convenient portable and economical surge protection. Small and powerful, the TRAVELCUBE features 750 joules and carries \$10K of insurance as well as a lifetime product warranty. Throw it in a briefcase or purse and have quality surge protection wherever you need it — hotel room, dorm, client office — anywhere!

#### **Features**

- Portable wall-mount cube stores easily in any bag or briefcase
- 1 NEMA5-15R AC outlet
- 750 joules of protection shields equipment from harmful surges, spikes and line noise
- Diagnostic LED displays protection status
- Built-in tel/modem surge protection
- UL 1449 rated 3rd Edition
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## **Specifications**

| OVERVIEW                           |                 |  |
|------------------------------------|-----------------|--|
| UPC Code                           | 037332118486    |  |
| INPUT                              |                 |  |
| Nominal Input Voltage(s) Supported | 120V AC         |  |
| Recommended Electrical Service     | 120V (110-125V) |  |
| Input Cord Length Details          | Direct plug-in  |  |





| Voltage Compatibility (VAC)       | 120  |  |
|-----------------------------------|--|--|
| Maximum Surge Amps                | 36000  |  |
| Input Plug Type                   | NEMA 5-15P   |  |
| Input Cord Length (ft.)           | 0  |  |
| Right-Angle Plug                  | No   |  |
| Input Cord Length (m)             | 0.00   |  |
| Integrated Cord Clip              | No   |  |
| OUTPUT                            |  |  |
| Frequency Compatibility           | 50 / 60 Hz   |  |
| Output Receptacles                | (1) 5-15R  |  |
| Circuit Breaker (amps)            | 15   |  |
| Transformer Accommodation         | (1) Yes  |  |
| Right-Angle Outlets               | Yes  |  |
| USER INTERFACE, ALERTS & CONTROLS |  |  |
| Diagnostic LED(s)                 | Yes  |  |
| Diagnostic LED Details            | Built-in LED confirms suppressor "protection present" (red) status           |  |
| SURGE / NOISE SUPPRESSION         |  |  |
| AC Suppression Joule Rating       | 750  |  |
| AC Suppression Response Time      | < 1 ns   |  |
| Protection Modes                  | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |  |
| UL1449 Let Through Rating         | 500V   |  |
| EMI / RFI Filtering               | Up to 20 dB  |  |
| Automatic Shut-Off                | No   |  |
| DATALINE SURGE SUPPRESSION        |  |  |
| Telephone/DSL Protection Details  | 1 line   |  |
| Cable (Coax) Protection           | No   |  |
| Network (Ethernet) Protection     | No   |  |
| Telephone/DSL Protection          | Yes  |  |
| PHYSICAL                          |  |  |
| Material of Construction          | Plastic  |  |
| Form Factors Supported            | Direct plug in suppressor supports wall-mounting directly into AC receptacle |  |
|                                   |  |  |
| Housing Color                     | Light Gray   |  |





| Receptacle Color   | Gray  |  |
|--|---|--|
| Shipping Dimensions (hwd / in.)                            | 1.50 x 4.25 x 6.50  |  |
| Shipping Dimensions (hwd / cm)                             | 3.81 x 10.80 x 16.51  |  |
| Shipping Weight (lbs.)                                     | 0.20  |  |
| Shipping Weight (kg)                                       | 0.09  |  |
| Unit Dimensions (hwd / in.)                                | 3.300 x 2.100 x 0.370   |  |
| Unit Dimensions (hwd / cm)                                 | 3.78 x 5.49 x 7.80  |  |
| Unit Weight (lbs.)   | .17   |  |
| Unit Weight (kg)   | 0.08  |  |
|  |   |  |
| FEATURES & SPECIFICATIONS                                  |   |  |
| Rotatable Outlets  | No  |  |
| Antimicrobial  | No  |  |
|  |   |  |
| STANDARDS & COMPLIANCE                                     |   |  |
| Product Certifications                                     | cUL Listed; UL 1449; UL 497A; UL 1363; UL Listed  |  |
| Product Compliance   | RoHS  |  |
|  |   |  |
| WARRANTY & SUPPORT   |   |  |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty   |  |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$10,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |  |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.