

## USB-C to HDMI Active Adapter Cable (M/M), 4K, Black, 3 ft. (0.9 m)

MODEL NUMBER: **U444-003-H**



Connects your existing HDMI TV, monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, smartphone or PC.

### Features

#### Connects an HDMI Display to Your USB-C or Thunderbolt 3 Device

- Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode
- Ideal for giving video presentations, editing multiple documents or streaming 4K video for digital signage
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps

#### Common Applications

- Extends 4K video from your primary display to another
- Duplicates the same video on 2 displays
- Converts a secondary display to your primary display

#### Crystal-Clear 4K Video and Digital Audio

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Supports 36-bit Deep Color (12 bits per channel)
- Supports per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR)

#### Reversible USB-C Connector

- Fumble-free reversible USB-C plug connects in either direction for quick connection every time

#### Premium Construction

- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Integral strain relief helps cable and connectors move freely without stress or cracking
- Durable PVC jacket designed to last a long time

### Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports UHD video resolutions up to 4K x 2K @ 30 Hz
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input

### Package Includes

- U444-003-H USB 3.1 Gen 1 USB-C to HDMI 4K Adapter Cable (M/M), 3 ft.

**Ready for Instant Use**

- Plug-and-play operation with no software, drivers or external power required
- 3 ft. length easy to manage in crowded environments
- Backward compatible with non-4K displays

## Specifications

OVERVIEW	
UPC Code	037332202475
Product Type	Active Cable
Technology	HDMI
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 30Hz
INPUT	
Bus Powered	Yes
Product Length (in.)	36
Product Length (cm.)	91.44
Product Length (ft.)	3
Product Length (m)	0.91
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
Power Consumption (Watts)	0.6
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
PHYSICAL	
Color	Black
Material of Construction	PVC, ABS
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1



Powering Business Worldwide



Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	1.00 x 7.00 x 9.50
Shipping Dimensions (hwd / cm)	2.54 x 17.78 x 24.13
Shipping Weight (lbs.)	0.19
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	1.000 x 7.000 x 9.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	2.1 BTU/Hr
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
IP68 Rated	No
IP20 Rated	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
HDCP Specification	1.4
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.