

Owner's Manual

USB 3.1 Gen 1 USB-C™ to USB-A Hub with Memory Card Reader and Charging

Model: U460-002-2AM-C

*USB Type-C and USB-C are trademarks of
USB Implementers Forum*

PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate peace of mind. You could also win an ISOBAR6ULTRA surge protector—a \$100 value!

www.tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA
www.tripplite.com/support

Copyright © 2016 Tripp Lite. All trademarks are the sole property of their respective owners.

Package Includes

- U460-002-2AM-C
- Owner's Manual

Optional Accessories

- U322-Series USB 3.0 A/B Device Cables
- U326-Series USB 3.0 Micro-B Device Cables
- U420-003 USB 3.1 Gen 1 USB-C Male/Male Cable – 3 ft.

Product Features

- Portable design with built-in cable is perfect for travel and stores easily into a laptop bag
- USB-A Hub ports support data transfer rates up to 5 Gbps and are compatible with previous USB generations
- Dedicated BC 1.2-compliant USB port provides up to 1.5A of fast charging power to mobile devices
- Micro SD and SD/MMC memory card slots allow external memory access via the USB-C port
- USB-C charging port charges your device and supports power input up to 20V 3A (60W)
- Plug-and-play – No software or drivers required

Installation

1. Connect the unit's USB Type-C connector to the USB-C port on your laptop, tablet or personal electronic device.
2. Connect up to two USB devices to the unit's USB-A Hub ports.
3. Insert a Micro SD or SD/MMC card into the corresponding memory card slot to access external memory.

Note: Only one memory card slot can be used at a time.

4. Charge your device by connecting the unit's USB-C port to your device's USB charger.

Specifications

Input Connectors	
USB	USB-C (Male)
Charging	USB-C (Female)
Output Connectors	
USB-A	USB A (Female) x2
Memory Card Slots	Micro SD x1 and SD/MMC x1
Environmental	
Operating Temperature	32 to 113°F (0 to 45°C)
Operating Humidity	10% to 85% RH, Non-Condensing
Storage Temperature	14 to 158°F (-10 to 70°C)
Storage Humidity	5% to 90% RH, Non-Condensing
Power Requirements	
USB-C Charging Port	Supports up to 20V 3A (60W) Input

Warranty and Product Registration

1-YEAR LIMITED WARRANTY

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of one (1) year from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way. EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser. EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

PRODUCT REGISTRATION

Visit www.triplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended. Do not use this equipment in the presence of a flammable anesthetic mixture with air, oxygen or nitrous oxide.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



1111 W. 35th Street,
Chicago, IL 60609 USA
www.triplite.com/support