

Quick Start Guide

100W Compact 4-Port USB-A/USB-C Wall Charger - GaN Technology, USB-C Power Delivery 3.0

Model: U280-W04-100C2G

Este manual esta disponible en español en la página
de Tripp Lite: www.tripplite.com/support

Ce manuel est disponible en français sur le site Web
de Tripp Lite : www.tripplite.com/support

WARRANTY REGISTRATION

Register your product today and be automatically entered to
win an ISOBAR® surge protector in our monthly drawing!

tripplite.com/warranty



Manufacturing
Excellence.

1111 W. 35th Street, Chicago, IL 60609 USA • tripplite.com/support

Copyright © 2020 Tripp Lite. All rights reserved.
USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum

Package Contents

- U280-W04-100C2G
- Quick Start Guide


Product Features

- Travel-sized wall charger with 2 USB-A and 2 USB-C ports provides up to 100W to quickly and efficiently charge your mobile device at home or on the road
- Gallium nitride (GaN) technology generates less heat to support high-efficiency charging
- Internal chip allows 100–240 VAC of input
- Connects to any NEMA 1-15R, 5-15R or 5-15R/20R AC outlet for immediate charging
- Protects your device against over-current, overload, over-voltage, over-temperature and short circuits
- Perfectly sized to carry in your suitcase, backpack or laptop bag for convenient travel use

Operation

1. Plug the power adapter into an AC wall outlet.
2. Connect one end of a user-supplied USB cable into the charger and the other end into the mobile device (smartphone, tablet, laptop, e-reader, etc.).
3. Disconnect the USB cable when the device is fully charged.

Note: If the charger stops working because of over-current, over-temperature or short circuit, disconnect the device immediately. Make sure the device is compatible with this charger before reconnecting it.



Specifications

Input/Output	
Input	100–240 VAC, 50/60 Hz
Output	USB-C Port 1: 5V–15V 3A, 20V 3.25A (output single: 20V 5A) USB-C Port 2: 5V 3A, 9V 2A USB-A Ports 3 & 4: 5V 3.4A (output single: 5V 2.4A)
Input Plug	NEMA 1-15P (non-polarized)
Protection	
Over-Current	Yes
Short Circuit	Yes
Over-Temperature	Yes
Over-Voltage	Yes

Specifications

Overload	Yes
Performance	
AC Leakage Current	5 max at 240 VAC input
Ripple and Noise	≤200mV
Turn-on delay time	3s max
Rise time	20 ms
Efficiency	Conform VI energy efficiency
Mechanical	
Color	White
Dimensions (H x W x D)	3.0 x 8.1 x 8.0 cm / 1.2 x 3.2 x 3.1 in.

Specifications

Weight	0.26 kg / 0.58 lb.
Environmental	
Operating Temperature Range	32° to 77°F / 0° to 25°C
Storage Temperature Range	-4° to 176°F / -20° to 80°C
Operating Humidity Range	20 to 90 % RH
Storage Humidity Range	5 to 90 % RH
Regulatory Approvals	
Main Unit	IEC/EN/UL 62368
Power Adapter	UL
Certifications	RoHS, REACH, FCC, UL, WEEE, ISO9001
Limited Warranty	
2 Years	

Warranty and Product Registration

1-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of 1 year from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, at its sole discretion.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND CONSEQUENTIAL DAMAGES. (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights, and you may have other rights that vary from jurisdiction to jurisdiction.)

WARNING: The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

PRODUCT REGISTRATION

Visit triplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



1111 W. 35th Street, Chicago, IL 60609 USA • tripplite.com/support