8-Port 1U Rack-Mount KVM Switch, PS/2

MODEL NUMBER: **B004-008**

Highlights

- Low Cost Switching Solution
- Does not require software or complicated setup simply Plug and Play
- Ultra-Compact – occupies only 1U rack space

System Requirements

- PS/2 mouse
- PS/2 keyboard
- Computer with PS/2 mouse and keyboard ports or an available USB port
- 1 P750-Series PS/2 KVM cable kit per PS/2 computer; or, 1 P750-Series PS/2 KVM cable kit and 1 B015-000 PS/2 to USB adapter per USB computer
- Compatible with all major operating systems

Package Includes

- 8 Port KVM Switch (Rackmount Ready)
- Optional AC Power Adapter - (Input: 100-240V, 50/60Hz, 0.5A Output: 9V/1.44A)
- Manual

Description

Tripp Lite's B004-008, 8-Port KVM Switch, is a low-cost solution for IT managers needing a KVM switch for up to 8 CPU's. Use on a desktop or in the rack; comes with 19" rackmount hardware. This switch provides two convenient methods to access any PC connected to the unit: Port Selection buttons located on the front panel, or, Hot-Key commands from the keyboard. A powerful Quick View Scan Mode feature allows you to auto-scan and monitor the activities of all installed operating PC's, one-by-one. Choose from three different cable lengths to connect from the switch to the CPU: P750-006, P750-010, or P750-015. (For computers with USB keyboard and mouse inputs, use Tripp Lite B015-000, PS/2 to USB converter, in conjunction with the P750 cable kit). For a more feature rich 8-port KVM switch, with On Screen Display (OSD) menu functions, as well as expandability, see Tripp Lite B042-008. Constructed of heavy-duty steel housing.

Features

- Control up to 8 PC's from a single console
- No software required - Switch between ports via front panel push buttons or hotkey commands
- Quick View Scan Mode for monitoring selected PC's
- PS/2 and Serial Mouse emulation provided for system boot-up
- Microsoft Intellimouse Pro, Logitech FirstMouse, FirstMouse+ support
- SVGA, VGA, and MultiSync monitor support
- Push Button LED display for easy status monitoring
- Rack mountable in 19" system rack - mounting hardware included with switch
- Hot Pluggable - add or remove PC's without powering down the switch
- Compatible with all major operating systems
- Superior Video Quality: 1920x1440; DDC2B
- Constructed of heavy-duty steel housing
- 19"W x 6"D x 1.75"H - 6.25lbs

Specifications

OVERVIEW	
UPC Code	037332125323
Console	No
Max CPU	8
Technology	PS/2; VGA/SVGA
POWER	
AC Adapter	(Input: 100-240V, 50/60Hz, 0.5A Output: 9V/1.44A)
CONNECTIONS	
Number of Ports	8
PC/Server Connections	VGA; USB; PS/2
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	4.25 x 21.75 x 11.50
Shipping Dimensions (hwd / cm)	10.80 x 55.24 x 29.21
Shipping Weight (lbs.)	6.80
Shipping Weight (kg)	3.08
Unit Dimensions (hwd / in.)	3.900 x 21.700 x 11.400
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 15.24
Unit Weight (lbs.)	6.25
Unit Weight (kg)	2.83
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys
IP Remote Access	Yes
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	1
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.