

USB-C Display Adapters

Models:

U444-06N-HD4K6B

U444-06N-DP4K6B

U444-06N-DP4K6W



Purchased product
may differ from image.

Este manual está disponible en español en la página de Eaton: Tripplite.Eaton.com/support

Ce manuel est disponible en français sur le site Web de Eaton : Tripplite.Eaton.com/support

Dieses Handbuch ist in deutscher Sprache auf der Eaton-Website verfügbar: Tripplite.Eaton.com/support

Questo manuale è disponibile in italiano sul sito web di Eaton: Tripplite.Eaton.com/support

EATON

Powering Business Worldwide

Product Features

- Add an additional 4K HDMI or DisplayPort™ monitor via the USB-C or Thunderbolt™ 3 port on your laptop, tablet or other device
- Supports USB DisplayPort Alternate Mode, allowing you to transmit an audio/video signal via the USB Type-C port on your smartphone, tablet, Ultrabook or computer
- U444-06N-HD4K6B supports HDMI 2.0a video resolutions up to 4096 x 2160 (4K x 2K) @ 60 Hz as well as HDCP 2.2 compatibility
- U444-06N-DP4K6B and U444-06N-DP4K6W supports video resolutions up to 3840 x 2160, UHD 4K (4K x 2K) @ 60 Hz
- Supports 24-bit Deep Color (8 bits per channel) max
- Supports max per lane data transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR)
- Supports 7.1 surround sound audio
- Thunderbolt 3 port compatible
- Specifically designed for use with the MacBook®, Google Chromebook Pixel™ and USB Type-C supported computers

Product Features

- Slim design is perfect for travel and stores easily in your laptop bag when not in use
- Plug-and-Play; no software or drivers required

Package Contents

- U444-06N-HD4K6B, U444-06N-DP4K6B or U444-06N-DP4K6W
- Owner's Manual

System Requirements

- USB Type-C or Thunderbolt 3 device that supports USB DisplayPort Alternate Mode
- DisplayPort or HDMI monitor

Optional Accessories

- P568-Series High-Speed HDMI Cables
- P569-XXX-CERT Premium High-Speed Cables with Gripping Connectors
- P580-Series DisplayPort Cables

Installation

- 1.** Connect the USB Type-C connector on the adapter to the USB Type-C port on your smartphone, tablet, Ultrabook or computer.
- 2.** Connect the DisplayPort or HDMI port on the adapter to a monitor using a DisplayPort or HDMI cable (such as P580-Series DisplayPort cables or P568-Series HDMI cables).
- 3.** The video image will appear on the add-on monitor. Customize how video is displayed on the add-on monitor using your device's display settings.

Specifications

	U444-06N-HD4K6B	U444-06N-DP4K6B / U444-06N-DP4K6W
Connectors-Input		
USB	USB-C (Male)	
Connectors-Output		
Ethernet	HDMI (Female)	DisplayPort (Female)
Video		
Maximum Resolutions	4096 x 2160, UHD 4K, @ 60 Hz	3840 x 2160, UHD 4K, @ 60 Hz
Color Depth	24-bit Deep Color (8 bits per channel)	
Environmental		
Operating Temperature	-4° to 158°F (-20° to 70°C)	
Storage Temperature	-4° to 185°F (-20° to 85°C)	
Relative Humidity	5% to 90% RH, Non-Condensing	

Warranty

3-Year Limited Warranty

We warrant our products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. Our obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. Visit Tripplite.com/support/product-returns before sending any equipment back for repair. This warranty does not apply to equipment which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, WE MAKE NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL WE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, we are not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

Warranty

FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense. The user must use shielded cables and connectors with this equipment. Any changes or modifications to this equipment not expressly approved by Eaton could void the user's authority to operate this equipment.

Warranty

WEEE Compliance Information for Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Eaton, they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Eaton has a policy of continuous improvement. Specifications are subject to change without notice.



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2023 Eaton
All Rights Reserved
Publication No.
23-08-102 /
93-36D3_RevE
August 2023

Eaton is a registered trademark.

All trademarks are property of their respective owners.