

NEW PRODUCT ANNOUNCEMENT



Tripp Lite Easy-Pull Long-Run Display Cables



- Detachable, Screw-On Connectors
- End Caps with Integrated Pull Tabs
- Stocked in 35, 50 & 100 ft. Lengths
- VGA, DVI & HDMI
- PVC or Plenum Rated Cable

Perfect For All Long-Run Video Applications

Tripp Lite Easy-Pull Long-Run Display Cables offer a simpler, safer method of connecting an A/V source to distant displays, up to 150 feet away. Tripp Lite Easy-Pull Cables feature detachable, screw-on connectors, allowing installers to easily pull the cable through conduit that normal monitor cables with bulky connectors simply can't fit into. Because the connectors are added after the cable is installed, Tripp Lite Easy-Pull Cables easily pull through drop ceilings, return air ducts and conduit as small as $\frac{3}{4}$ inches in diameter—even with factory-manufactured 90° bends.* With more cable installation options, Easy-Pull Cables make it easier to meet stringent building codes. Easy-Pull Cables are perfect for all long-run video applications: video signage used in retail or public sectors, video monitors used in home-/business-theaters, schools/training facilities and more.

* Field-manufactured bends may result in smaller diameter or flattened conduit at the point of the bend.

Saves Time and Helps You Meet Building Codes

Detachable, Screw-On Connectors

- Eliminate need to field-terminate cables
- Allow cable to be run to code—inside conduit, drop ceilings, etc.

Simplifies Cable Pulls & Safeguards Cable



Integrated Pull Tabs & Threaded End Caps

- Make pulling long cables fast and easy
- Protect entire cable from strain and contacts from dirt or damage
- Safely support up to 30 lbs. of pull force

Superior Cable Ends


Tripp Lite Easy-Pull Cables feature threaded end caps with integrated pull tabs. The tabs safely support more pull-force than the average cable—up to 30 lbs.—safeguarding the cable from damage. The threaded end caps protect the connector contacts from dirt or damage during installation. To finish the installation, simply attach the appropriate combination of connectors for the cable. For convenience, cables and connectors are available separately or as all-in-one kits. All Tripp Lite connectors are packaged in pairs.

Premium Cable Construction

Tripp Lite Easy-Pull Long-Run Display Cables feature premium molded connectors, which stand up to demanding applications better than cables with assembled connectors. Color-coded cable ends ensure a perfect match between cables and detachable connectors. Double shielding (foil and braid) provides maximum EMI/RFI protection. Type A Cables (for VGA applications) are comprised of three copper braided UL1354 coax cables, four twisted-pair cables and two signal cables. Type B Cables (for digital cables such as DVI and HDMI) are comprised of four UL20276 individually-shielded, twisted-pair cables with drain-wire, one twisted-pair cable and five signal cables.

See Back for Specifications

Typical Application



* Connection cable available separately from Tripp Lite.

SPECIFICATIONS

Type A Cable—for VGA Video Applications

Select the Cable → Then Choose the Desired Connector Kit

"Type A" Cables (use with "Type A" Connectors)

Model #	Description*
EZA-035	35 ft. Cable
EZA-035-P	35 ft. Cable (Plenum)
EZA-050	50 ft. Cable
EZA-050-P	50 ft. Cable (Plenum)
EZA-100	100 ft. Cable

* Custom lengths are available.

"Type A" Connectors (Set of 2 Connector Ends Per Package) (use with any "Type A" Cable)

Model #	Application	Connectors
EZA-VGAM-2	VGA Cable	Two HD15 (M)
EZA-VGAF-2	VGA Extension Cable	Two HD15 (F)*
EZA-VGAX-2	VGA Extension Cable	HD15 (M), HD15 (F)*
EZA-VGAAM-2	VGA Cable with Audio	Two HD15 (M) with 3.5mm (M)
EZA-VGAAF-2	VGA Extension Cable with Audio	Two HD15 (F) with 3.5mm (F)*
EZA-VGAAX-2	VGA Extension Cable with Audio	HD15 (M) with 3.5mm (M), HD15 (F) with 3.5mm (F)*

* Includes a wall faceplate for each female connector. M = Male, F = Female.



Purchase Cables & Connectors Together

All-In-One Cable/Connector Kits

Model #	Description	Connectors
P501-050	50 ft. Extension Cable with VGA Connectors	HD15 (M/F)
P501-100	100 ft. Extension Cable with VGA Connectors	HD15 (M/F)
P503-050	50 ft. Cable with VGA Connectors	HD15 (M/M)
P503-100	100 ft. Cable with VGA Connectors	HD15 (M/M)
P504-050-EZ	50 ft. Cable with VGA Connectors & with Audio	HD15 (M/M/3.5mm)
P504-100-EZ	100 ft. Cable with VGA Connectors & with Audio	HD15 (M/M/3.5mm)

M = Male, F = Female.

Type B Cable—for Digital DVI & HDMI Video Applications

Select the Cable → Then Choose the Desired Connector Kit

"Type B" Cables (use with "Type B" Connectors)

Model #	Description*
EZB-050	50 ft. Cable*
EZB-100	100 ft. Cable*

* Plenum available on request. Custom lengths are available.

"Type B" Connectors (Set of 2 Connector Ends Per Package) (use with any "Type B" Cable)

Model #	Application	Connectors
EZB-DVIM-2	DVI Cable*	Two DVI-D (M)
EZB-DVIF-2	DVI Extension Cable*	Two DVI-D (F)**
EZB-DVIX-2	DVI Extension Cable*	DVI-D (M), DVI-D (F)**
EZB-HDMIM-2	HDMI Cable*	Two HDMI (M)

* Requires extender, listed below. ** Includes a wall faceplate for each female connector. M = Male, F = Female.



Purchase Cables & Connectors Together

All-In-One Cable/Connector Kits

Model #	Description	Connectors
P561-050-EZ	50 ft. DVI Cable with Connectors*	DVI-D (M/M)
P561-100-EZ	100 ft. DVI Cable with Connectors*	DVI-D (M/M)
P568-050-EZ	50 ft. HDMI Cable with Connectors*	HDMI (M/M)
P568-100-EZ	100 ft. HDMI Cable with Connectors*	HDMI (M/M)

* Requires extender, listed below. M = Male.

Optional Accessories

Model #	Description	Connectors
B120-000	DVI Extender (extends range to 150 ft.)	DVI (F/F)
B122-000	HDMI Extender (extends range to 150 ft.)	HDMI (F/F)
B123-001	HDMI 1 ft. Extender Cable with Integrated Signal Booster (extends range to 150 ft.)	HDMI (M/F)
P166-001-P	HDMI Wall Plate	HDMI (F/F)
P166-001-A	HDMI Wall Plate with Integrated Signal Booster (extends range to 150 ft.)	HDMI (F/F)
A152-000-2	HDTV Fully-Loaded Wall Plate Kit (with two interchangeable bezels)	HDMI (F/F), RCA x5 (F/F) Coax x2 (F/F), RJ11 (F/F)

M = Male, F = Female. The policy of Tripp Lite is one of continuous improvement. Specifications are subject to change without notice. Actual product may differ slightly from photos.

Tripp Lite offers a complete line of KVM switches, cables and connectivity products!

Visit www.tripplite.com for complete specifications.

