

## DVI to VGA Y Splitter Adapter Cable (DVI-I to HD15 M/2xF), 1 ft. (0.3 m)

MODEL NUMBER: P120-001-2



Ideal for conference rooms and sales presentations where two VGA or DVI-I monitors or projectors must be simultaneously fed from a single DVI-I or VGA signal while delivering superior video quality.

### Features

- Connect two VGA monitors to a single DVI-I port or connects two DVI-I monitors to a single VGA port
- 1 ft. DVI-A Analog Male to 2 x VGA (HD15) Female Cable
- Fully molded construction and double-shielding ensures long life
- Superior video quality; supports video resolutions up to 2048 x 1536
- RoHS Compliant

## Specifications

OVERVIEW	
UPC Code	037332142238
Product Type	Passive Cable
Technology	DVI; VGA/SVGA
CONNECTIONS	
Side A - Connector 1	DVI-A (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

### Highlights

- Splits a DVI-A Analog signal to connect two VGA-enabled devices to a single DVI-I port or connects two DVI-I enabled devices to a single VGA port
- Ideal solution when you need to display a video signal to 2 monitors for presentations.
- Fully molded construction and double-shielding guarantees long life
- Superior video quality; supports video resolutions up to 2048 x 1536

### System Requirements

- DVI-I enabled computer (supports both Analog and Digital) or VGA enabled computer

### Package Includes

- 1 ft. DVI-A Analog Male to 2 x VGA (HD15) Female Cable



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Jacket Rating	VW-1
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.