

# SmartRack 9U Low-Profile Switch-Depth Wall-Mount Mini Rack Enclosure

MODEL NUMBER: SRW9U



Houses, secures and organizes switches and other rack-mount equipment in server closets, classrooms, offices and other areas with limited floor space.

## Features

### Switch-Depth 9U Server Cabinet Accommodates 19 in. Rack Equipment

This SmartRack® 9U rack enclosure is designed for home and office network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the SRW9U has a maximum stationary load capacity of 200 pounds (91 kilograms).

### Keeps Important Equipment Secure

The reversible front door and removable side panels lock securely to help prevent damage, tampering or theft. The doors and side panels are designed for quick release, making it simple to access connected equipment and cabling with little effort. Convenient top and bottom access panels allow easy cable routing through the cabinet. The vented doors and sides, as well as vents on the top and bottom, allow generous airflow from front to rear and top to bottom to keep your equipment cool and functioning at its peak.

### Easy Enclosure and Equipment Installation

This 9U server rack comes fully assembled for quick and easy deployment. Front and rear vertical rails with square mounting holes accept standard rack equipment up to 16.5 inches (419 millimeters) deep, such as network switches, routers and patch panels. Hardware is included for wall-mounting the SRW9U. You can also use the optional SRCASTER kit (sold separately) to install metal casters to the rack and roll it along a level surface.

### Meets Payment Card Industry Standards

The SRW9U provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or transmit credit card information.

## Highlights

- 9U rack constructed from powder-coated steel that stands up to tough environments
- Houses switches, routers and other equipment up to maximum 200 lb. load capacity
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Ships fully assembled for immediate deployment and equipment mounting
- Provides physical equipment and media security required for PCI DSS compliance

## Package Includes

- SRW9U 9U Server Rack
- (12) M6 screws
- (12) M6 cage nuts
- (12) M6 cup washers
- Removable mounting plate
- (3) Mounting plate screws
- (2) Keys
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332160744



Powering Business Worldwide



Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Small Enclosure
<b>PHYSICAL</b>	
Color	Black
Rack Height	9U
Rack Depth	Shallow
Maximum Device Depth (cm)	41.91
Maximum Device Depth (in.)	16.5
Maximum Device Depth (mm)	419
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Shipping Dimensions (hwd / in.)	22.60 x 20.60 x 26.40
Shipping Dimensions (hwd / cm)	57.40 x 52.32 x 67.06
Shipping Weight (lbs.)	39.00
Shipping Weight (kg)	17.69
Unit Dimensions (hwd / in.)	19.750 x 23.630 x 17.690
Unit Dimensions (hwd / cm)	50.5 x 60.02 x 45.16
Unit Weight (lbs.)	35
Unit Weight (kg)	15.88
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	2
<b>FEATURES &amp; SPECIFICATIONS</b>	
Grounding Details	Front and Back door frames
Built-in Cable Management	No
Extra Wide	No
Locking	No
Pre-Installed Casters	No
Outdoor Use	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 60950-1
Product Compliance	RoHS; EIA/ECA-310-E; UKCA



Powering Business Worldwide



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.