



3-Port USB-C Hub with Card Reader, USB 3.x (5Gbps) Hub Ports and Card Reader Ports, White

MODEL NUMBER: U460-003-3AM











Adds 3 USB-A ports and memory card slots to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook, tablet or notebook.

Features

USB-C 3.1 Hub Connects USB Peripherals to Your USB-C or Thunderbolt 3 Device

This USB-C hub allows you to connect up to three USB peripherals to your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC. This lets you expand the potential of your device by connecting USB peripherals, such as an external hard drives, flash drives, power meters and printers. You can also insert a memory card into the corresponding slot to transfer data. The memory card reader supports MicroSD, SD, SDHC, SDXC and MMC cards for convenient access to digital photos, camcorder videos, smartphone data and other essential files. Only one memory card may be used at a time.

Connects USB Peripherals and Transfers Data at Fast USB 3.1 Gen 1 Speeds

In addition to accepting USB peripherals, the USB ports provide up to 0.9 amps each for charging and powering smartphones and other mobile devices. All three USB ports and the memory card slot transfer data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Note: Host must support USB OTG (On-the-Go)

Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package

The plug-and-play USB Type-C hub is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. It's about the size of a credit card to make it easy to carry in a pocket, backpack or laptop bag for use anywhere.

Highlights

- USB-C 3.1 Type-C hub is compatible with all USB-C and Thunderbolt 3 devices
- Connects external hard drives, keyboard, printer and other USB peripherals
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Charge and power a tablet, smartphone or other compatible mobile device
- Connect up to 3 USB peripherals, such as an external hard drive, flash drive and printer
- Transfer photos, videos and other important files between your MacBook or Chromebook and a memory card

System Requirements

 Device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

Package Includes

- U460-003-3AM USB 3.1 Gen 1 USB-C Hub, 5 Gbps, White
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332193766





Product Type	Hub	
Technology	USB 3.x	
Host Connector	USB C (MALE)	
VIDEO		
Number of Monitors Supported	0	
Extended Mode	No	
Mirror Mode	No	
DATA		
Data Ports	(3) USB A (FEMALE)	
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)	
STORAGE		
Card Slots	SD (FEMALE); MICRO SD (FEMALE)	
Card Slots Details	SD 3.0 Memory Card slots (SD and MicroSD)	
INPUT		
Bus Powered	Yes	
Product Length (in.)	6	
Product Length (cm.)	15.24	
Product Length (ft.)	0.5	
Product Length (m)	0.15	
BATTERY		
Battery Charging (5V/1.5A Port)	No	
POWER		
Power Consumption (Watts)	2.4	
CONNECTIONS		
Number of Ports	5	
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	(3) USB 3.0 A (FEMALE)	
Side B - Connector 2	MICRO SD (FEMALE)	
Side B - Connector 3	SD (FEMALE)	
Connector Plating	Nickel	
CHARGING		





Charging Ports / Amps	(3) 0.9A	
PHYSICAL		
Color	White	
Material of Construction	Plastic	
Cable Jacket Rating	VW-1	
Shipping Dimensions (hwd / in.)	0.90 x 4.00 x 5.60	
Shipping Weight (lbs.)	0.16	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
Unit Packaging Type	Вох	
Unit Weight (lbs.)	0.11	
Unit Weight (kg)	0.05	
ENVIRONMENTAL		
Operating Temperature Range	32° to 113°F (0° to 45°C)	
Storage Temperature Range	14° to 158°F (-10° to 70°C)	
BTUs	8.2	
Operating Humidity Range	10 - 85 % RH	
Storage Humidity Range	5 - 90 % RH	
FEATURES & SPECIFICATIONS		
USB Hub Ports	Yes	
Number of USB Hub Ports	3	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)	
UASP Support	Yes	
Auto MDIX Support	No	
Full Duplex Support	No	
Suspend Mode Support	No	
Remote Wakeup Support	No	
SD Card Specification	SD; Micro SD	
Driver Required	No	
STANDARDS & COMPLIANCE		
TAA Compliant Option	N	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		





Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.