

Audio Cables (2 x RCA M/M), 6-ft.

MODEL NUMBER: A050-006



Description

Tripp Lite's premium High Resolution Gold Audio Cables are designed to provide a clear, accurate sound, as well as eliminate noise and interference that can compromise your listening pleasure. This 6 ft. cable is specifically designed for digital devices, providing better sonic accuracy and more detailed, natural sound. This cable features 75 ohm coaxial cable, made of 99.99% pure copper, and precision machined, 6-cut, Gold RCA connectors that are corrosion resistant.

Features

- Superb audio clarity with more natural sounding mid-range
- Premium-grade, 99.99% pure copper conductors
- Nitrogen-injected dielectric material delivers better high frequencies and a more realistic stereo image
- 6-cut RCA connectors, with split-tip center pin, ensure a precise connection
- 24kt gold plating resists corrosion and provides increased durability
- Molded, color coded connectors
- Abrasion resistant flexible PVC jacket

Specifications

| OVERVIEW | |
|--------------------------------|----------------|
| UPC Code | 037332121899 |
| Technology | Stereo Audio |
| CONNECTIONS | |
| Side A - Connector 1 | (2) RCA (MALE) |
| Side B - Connector 1 | (2) RCA (MALE) |
| Latching or Gripping Connector | No |

Highlights

- Superior audio quality for movies with Dolby Digital and DTS Surround-Sound
- High-purity copper coax for improved signal transfer and low energy loss
- Double-shielded construction for maximum EMI/RFI protection
- Silver-plated center conductor for the best high frequency response

System Requirements

- Home Theater or Stereo equipment with RCA Digital Audio connectors

Package Includes

- 6 ft. High Resolution Gold Audio Cable



Powering Business Worldwide



| PHYSICAL | |
|-------------------------------------|---------------------------|
| Color | Black |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 9.50 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 24.13 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.58 |
| Shipping Weight (kg) | 0.26 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.