

USB 3.0 SuperSpeed Active Repeater Cable (A to B M/M), 25 ft. (7.62 m)

MODEL NUMBER: U328-025



Locate a printer or other USB peripheral 25-ft. from your computer.

Description

This USB 3.0 Active A/B cable overcomes the 16-foot (five-meter) USB distance limitation with an active repeater in the middle of the cable. Now USB printers and other devices can be located up to 25 feet (7.6 meters) away from the computer in a single, non-daisy-chainable run with no need for extension cables. Full 5 Gbps speed is maintained along the entire length of the cable. Backward compatible to USB 1.1 and 2.0. Plug-and-play, Windows and macOS compatible.

Features

- Connect a computer to a printer or other USB device up to 25-ft. (7.62 m) away
- SuperSpeed USB 3.0, Hi-Speed 2.0 and USB 1.1 compatible
- Active repeater maintains 5Gbps signal integrity
- USB "A" to USB "B" connections
- Windows 98/ME/2000/XP/Vista/WIN7/8/10 and MAC compatible
- Cable length: 25-ft. (7.62 m) Weight: 1 lb.
- Repeater Pod dimension: 16.75 x 57.3 x 31.7 (mm.) / 0.7 x 2.3 x 1.3 (in.)

Highlights

- 25-ft. (7.62 m) USB3.0 SuperSpeed A-B Active Cable
- Overcomes the 5-meter USB barrier
- Built-in repeater maintains SuperSpeed USB 3.0 signal quality

System Requirements

- A USB 3.0 port and USB 3.0 device (with type B jack) are required to meet USB 3.0 speeds. A USB 2.0 or 1.1 port and/or device can be used, but you will not be able to achieve USB 3.0 speeds.
- Not for use with Xbox (see Xbox website for details on extending devices with Xbox)

Package Includes

- 25-ft. (7.62 m) SuperSpeed USB3.0 A/B Active Device Cable (A Male to B Male)

Specifications

OVERVIEW	
UPC Code	037332181831
Technology	USB 3.x
Cable Type	Active
CONNECTIONS	



Powering Business Worldwide



Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 B (MALE)
Connector Style	Straight
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	25
Cable Length (m)	7.62
Shipping Dimensions (hwd / in.)	10.63 x 9.06 x 0.50
Shipping Dimensions (hwd / cm)	27.00 x 23.01 x 1.27
Shipping Weight (lbs.)	1.10
Shipping Weight (kg)	0.50
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.