

NetDirector USB Server Interface Unit with Virtual Media Support (B064-Series)

MODEL NUMBER: B055-001-USB-V2



Description

This USB Server Interface Unit with Virtual Media support connects a USB server to a B064-IPG Series NetDirector® KVM switch using Cat5e/6 cabling. The server connected using this interface unit will be able to access the Virtual Media functionality of the B064-IPG series KVM switch. Use of Cat5e/6 cables frees up space in server cabinets that would otherwise be filled by traditional, bulkier KVM cable kits. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.
 Note: SIUs that were purchased prior to that of your KVM switch may require a firmware upgrade in order for them to work properly (see Maintenance under OSD Operation section of your B064-Series KVM Owner's Manual for details).

Features

- Provides the connected server with access to Virtual Media
- Eliminates the need for thicker, heavier KVM cable kits
- Compact, lightweight design
- Plug and Play; no software required
- No power supply required
- 164 ft. (50 m.) distance from KVM switch
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332151742
Accessory Type	Server Interface Unit
Technology	Cat5/5e; VGA/SVGA
Accessory Class	KVM Switch Accessories

Highlights

- Connect a USB server to a B064- IPG Series NetDirector KVM switch via Cat5e/6 cable
- Provides the connected server with access to Virtual Media
- Allows a maximum distance of 164 ft. (50 m.) from KVM to Server via Cat5e/6 cable
- Compact and lightweight design
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Server or CPU with a HD15 connector and USB type A connector
- A B064- IPG Series NetDirector Cat5 KVM Switch
- Cat5e/6 cable

Package Includes

- USB Server Interface Unit with Virtual Media support



Powering Business Worldwide



PHYSICAL	
Shipping Dimensions (hwd / in.)	1.70 x 5.10 x 4.90
Shipping Dimensions (hwd / cm)	4.32 x 12.95 x 12.45
Shipping Weight (lbs.)	0.55
Shipping Weight (kg)	0.25
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.