

## Mini USB VGA over Cat5 UTP KVM Console Extender Kit - 230-ft.

MODEL NUMBER: 0DT23010



### Description

The Mini KVM Extender USB is a high value, affordable solution for extending your KVM console from your computer or KVM switch to a distance of up to 230-ft. (70M) away over clutter free CAT5/6/7 cables.

If you're working from a small, home office (SOHO), the Mini KVM Extender USB is your preferred extended control solution - just place the KVM console where you want and the computer where you need and you're all set to go!

For industrial applications such as manufacturing lines or clean rooms, the Mini KVM Extender USB provides maximum safety and security, allowing you to place computers and servers in a single centralized location, far away from any production hazards.

IT managers seeking extended access to server rooms in a tightly secured environment will find the Mini KVM Extender USB particularly efficient and easy to use. Ideal also for presentation and training applications, the Mini KVM Extender USB provides flexibility and security coupled with highly attractive pricing.

The Mini KVM Extender USB is made up of 2 micro sized, compact units on both ends: a Transmitter unit with VGA and USB connectors that connects to the computer / KVM switch, and a Receiver unit with VGA and PS/2 connectors that connects to the remote keyboard, monitor and mouse. The Mini KVM Extender USB is a pure hardware solution, making it both software and network independent.

### Features

- Manage a USB computer or KVM switch from a remote location up to 230-ft. (70M) away
- More security - Look after your investment by storing computers in locked, environmentally controlled room
- More flexibility - Place your KVM console where you want it and your computer where you need it
- More efficiency - Make your set up work for you instead of you working for your set up

### Highlights

- Manage a USB computer or KVM switch from a remote location up to 230-ft. (70M) away
- More security - Look after your investment by storing computers in locked, environmentally controlled room
- More flexibility - Place your KVM console where you want it and your computer where you need it
- More efficiency - Make your set up work for you instead of you working for your set up
- Plug and play solution
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- Compatible with all major operating systems
- Computer or KVM switch with VGA and USB ports
- VGA monitor and PS/2 keyboard and mouse

### Package Includes

- Local Transmitter Unit
- Remote Receiver Unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz Output: DC5V/1000mA)
- Owner's Manual



Powering Business Worldwide



- Plug and play solution
- Micro sized - Smallest form factor for sleek Transmitter and Receiver units. Once installed you won't even know they exist!
- Transmitter unit features VGA and USB connectors for the computer / KVM switch, and the Receiver unit features VGA and PS/2 connectors for the remote keyboard, monitor and mouse
- Simple to install and operate
- No external power needed at transmitter end
- Supports all major OS
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	654518301670
Accessory Type	Extender Kit
Technology	VGA/SVGA
Accessory Class	KVM Switch Accessories
INPUT	
Redundancy - Dual Power Inputs	No
Bus Powered	No
POWER	
AC Adapter	(Input: 100-240V, 50/60Hz Output: DC5V/1000mA)
CONNECTIONS	
PC/Server Connections	VGA; USB
PHYSICAL	
Color	Black
Rackmountable	No
Shipping Dimensions (hwd / in.)	6.00 x 4.20 x 6.80
Shipping Dimensions (hwd / cm)	15.24 x 10.67 x 17.27
Shipping Weight (lbs.)	1.30
Shipping Weight (kg)	0.59
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Operating Temperature	0 TO 40 C / 32 to 104 F
FEATURES & SPECIFICATIONS	



Powering Business Worldwide



On-Screen Display (OSD)	No
Driver Required	No
<b>REMOTE ACCESS</b>	
Modem Port	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.