

# CPU / Computer Mount for Desks and Rails

MODEL NUMBER: DCPU1



Secures your computer to a wall, desk or rail, which saves valuable desk, table and floor space near your workstation. Ideal for home, school or office use.

## Description

The DCPU1 CPU/Computer Mount saves valuable desk, table and floor space by securing your computer to a wall, desk or rail. Ideal for home, school and office use beneath, above or adjacent to your workstation, the DCPU1 fits most CPUs from 4 to 6.25 inches wide. Its adjustable open frame allows easy access to the CPU and its cabling. The durable all-metal unit supports up to 40 lbs (18.1 kgs). The scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Wall-mounting hardware is included.

## Features

### Saves Valuable Desk, Table and Floor Space

- Mounts your computer to wall, desk or rail
- Adjustable frame fits most CPUs from 4 to 6.25 in. wide
- Wall-mounting hardware included
- Ideal for home, school or office use beneath, above or adjacent to your workspace

### Durable Metal Construction

- Supports up to 40 lbs (18.1 kgs)
- Scratch-resistant powder-coated finish blends with any décor
- Open frame design allows easy access to CPU and cabling

## Highlights

- Fits most CPUs from 4 to 6.25 in. wide
- Open frame design allows easy access to CPU and cabling
- Wall-mounting hardware included
- Supports up to 40 lbs (18.1 kgs)

## Package Includes

- Punched bracket half
- Slotted bracket half
- (2) Knobs
- Foam block
- (2) Drywall screws
- (2) Drywall anchors
- (2) Washers
- (12) Foam discs
- Owner's manual

# Specifications

| OVERVIEW             |              |
|----------------------|--------------|
| UPC Code             | 037332181671 |
| Device Compatibility | Monitor/HDTV |
| PHYSICAL             |              |



Powering Business Worldwide



|                                      |                                 |
|--------------------------------------|---------------------------------|
| Color                                | Gray                            |
| Material of Construction             | Steel                           |
| Motion                               | Fixed                           |
| Mounting Location                    | Wall                            |
| Degrees of Motion                    | Fixed                           |
| Maximum Weight Capacity (lbs.)       | 40                              |
| Maximum Weight Capacity (kg)         | 18                              |
| Shipping Dimensions (hwd / in.)      | 4.29 x 4.48 x 11.33             |
| Shipping Dimensions (hwd / cm)       | 10.90 x 11.38 x 28.78           |
| Shipping Weight (lbs.)               | 4.98                            |
| Shipping Weight (kg)                 | 2.26                            |
| Unit Dimensions (hwd / in.)          | 6.100 x 6.100 x 10.030          |
| Unit Dimensions (hwd / cm)           | 1.71 x 25.5 x 10.4 - 16.4       |
| Unit Weight (lbs.)                   | 4.4                             |
| Unit Weight (kg)                     | 2.00                            |
| Assembly Required                    | Yes                             |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                 |
| Antimicrobial                        | No                              |
| Cord Management                      | No                              |
| Tools Necessary                      | Yes                             |
| Security Lock                        | No                              |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                 |
| Product Compliance                   | RoHS; RoHS3; CE (Europe); REACH |
| <b>WARRANTY &amp; SUPPORT</b>        |                                 |
| Product Warranty Period (Worldwide)  | 5-year limited warranty         |

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.