

# Full Motion Desk Mount for 13" to 27" Monitors - clamp and grommet

MODEL NUMBER: DDR1327S



Mounts a monitor off the surface of your desk, table or workstation by either a clamp or grommet to free up valuable space. Ideal for home or office use.

## Description

The VESA-compliant DDR1327S Full Motion Desk Mount Clamp attaches to your desk, table or workstation, allowing you to mount a monitor above it and free up valuable workspace. Ideal for home and office, the DDR1327S fits most flat-panel displays from 13 to 27 inches. Grommet hardware is also included.

The swivel arm can be independently adjusted for angle and height to give you maximum flexibility in positioning your display to fit your environment and comfort level. Move the screen closer to you, or push it out of your way when not in use. A 180° swivel and -40° to +90° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitor in portrait or landscape orientation.

Durable clamp attaches to most flat surfaces up to 3.5 inches thick with a firm grip. Swivel arm supports monitors up to 20 lbs (9 kgs). The durable all-metal frame with soft rubber-feel finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm.

## Features

**Attaches to Most Desks, Tables and Workstations** Clamps securely to most flat surfaces from 0.4 in. to 3.5 in. Grommet hardware also included Fits most flat-panel displays from 13 to 27 in. Swivel arm adjusts independently for angle and height Ideal for home and office use

**Convenient One-Touch Adjustment** 180° swivel and -40° to +90° tilt capability provides comfortable viewing Full 360° rotation for viewing in portrait or landscape orientation

**Durable Metal Construction** Supports monitors up to 20 lbs (9 kgs) Soft rubber-feel finish blends with any décor Mounting hardware included Display cable attaches to mount to reduce clutter

**VESA Compliance** Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm

## Specifications

### Highlights

- Fits most flat-panel displays from 13 to 27 in.
- Mounts by clamp or grommet
- One-touch adjustment for comfortable viewing
- 180° swivel and -40° to +90° tilt for wide range of motion
- Supports monitors up to 20 lbs (9 kgs)

### Package Includes

- Adapter bracket assembly
- Pole
- Desk clamp assembly
- Grommet assembly
- (4) M4 screws
- (4) M5 screws
- (4) D5 washers
- Base plate
- Pad
- Hex key, 3 mm
- Hex key, 4 mm
- Hex key, 5 mm
- Hex key, 6 mm
- Owner's manual



Powering Business Worldwide



OVERVIEW	
UPC Code	037332183460
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full
Mounting Location	Desk Clamp; Grommet
Degrees of Motion	-40/+90 Tilt; 180 Swivel; 360 Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	20
Maximum Weight Capacity (kg)	9
Min/Max Arm Extension (in.)	19.68
Min/Max Arm Extension (cm)	50
Number of Displays	1
Shipping Dimensions (hwd / in.)	15.80 x 5.40 x 16.50
Shipping Dimensions (hwd / cm)	40.13 x 13.72 x 41.91
Shipping Weight (lbs.)	11.70
Shipping Weight (kg)	5.31
Unit Dimensions (hwd / in.)	20.070 x 6.300 x 23.700
Unit Dimensions (hwd / cm)	50,98 x 49,99 4,91
Unit Weight (lbs.)	11.55
Unit Weight (kg)	5.24
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No



Powering Business Worldwide



STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.