



Easy Pull Type-A Connectors - F/F set of VGA, 3.5mm, RCA Audio, Composite Video

MODEL NUMBER: EZA-VGACSAF-2



Highlights

- SVGA / 3.5mm / Red-White RCA Audio / Composite Video, Female to Female
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

Package Includes

2 x HD15/3.5mm/Red White RCA Audio/Composite Video, All female Jacks, with wallplates

Description

Easy Pull Connector Kit includes: 2 x HD15 Female, 2 x stereo 3.5mm jack, 4 x RCA Red/White Audio jacks, and 2 x Yellow Composite Video jack, with 2 x faceplates and 1 ft. pigtails. Video support up to 1600 x 1200. Use with either PVC or Plenum Easy Pull trunk cables.

Features

- Easy Pull, SVGA / 3.5mm / Red-White RCA Audio / Composite Video, Female to Female
- Eliminates the need to field terminate VGA connectors
- Allows cable to be run according to code inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35 ft., 50 ft. and 100 ft. lengths, PVC or Plenum rated jackets
- Support resolutions up to 1600 x 1200

Specifications

OVERVIEW		
UPC Code	037332153784	
Technology	Composite; Stereo Audio; VGA/SVGA	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	HD15 (FEMALE)	
Side A - Connector 2	3.5MM (FEMALE)	
Side A - Connector 3	DIN 14 PIN (MALE)	
Side B - Connector 1	HD15 (FEMALE)	





Side B - Connector 2	3.5MM (FEMALE)	
Side B - Connector 3	DIN 14 PIN (MALE)	
Latching or Gripping Connector	No	
PHYSICAL		
Color	Black; Green	
Cable Length (ft.)	0.5	
Cable Length (m)	0.15	
Shipping Dimensions (hwd / in.)	2.00 x 6.20 x 9.10	
Shipping Dimensions (hwd / cm)	5.08 x 15.75 x 23.11	
Shipping Weight (lbs.)	0.80	
Shipping Weight (kg)	0.36	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.