



Powering Business Worldwide

# 14-ft. Cat5e 350 MHz Snagless Molded Cable (RJ45 M/M) - Gray

MODEL NUMBER: **N001-014-GY-R**



### Description

Tripp Lite's 14-ft. gray snagless category 5e (Cat5e) patch cable has 2 snagless RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair stranded UTP and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Standard category 5e patch cables are also available.

### Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 14-ft. color: gray connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002 series)
- Also available - Cat6 cables (N201 series)

## Specifications

OVERVIEW	
UPC Code	037332012579
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)

### Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors
- Retail packaging

### System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

### Package Includes

- 14Ft Gray Snagless Cat5e Patch Cable



Powering Business Worldwide

Side B - Connector 1	RJ45 (MALE)
<b>PHYSICAL</b>	
Color	Gray
Cable Shielding	UTP
Cable Length (ft.)	14
Cable Length (m)	4.27
Shipping Dimensions (hwd / in.)	0.27 x 0.27 x 0.08
Shipping Dimensions (hwd / cm)	0.69 x 0.69 x 0.20
Shipping Weight (lbs.)	0.27
Shipping Weight (kg)	0.12
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.