



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: P002-002

### 2-ft. Power Cord (IEC-320-C14 to NEMA 5-15R)

#### Highlights

- 2-ft. UL-listed power cord
- Allows you to plug a power cord with an NEMA 5-15P into an IEC-320-C13 outlet in a PDU or CPU.
- Frees up a wall outlet
- Plug type: IEC-320-C14 (CPU) to NEMA 5-15R



#### Description

Tripp Lite makes your PC installation one step easier. This 2-ft. AC Power Adapter Cord allows you to plug a power cord with an NEMA 5-15P into an IEC-320-C13 outlet in a PDU or CPU. Installation with convenience is the name of the game. Features a NEMA 5-15R receptacle with an IEC-320-C14 plug.

#### System Requirements

- A monitor with an AC power cord (NEMA 5-15P)
- A computer with an available power receptacle (IEC-320-C13)

#### Package Includes


- 2-ft. AC power adapter cord PC style male (IEC-320-C14) to AC female (NEMA 5-15R)

#### Features

- UL-listed
- Allows you to plug a power cord with an NEMA 5-15P into an IEC-320-C13 outlet in a PDU or CPU.
- Frees up a wall outlet
- Plug type: IEC-320-C14 (CPU) to NEMA 5-15R
- 16AWG SJT, 12A, 125V

#### Specifications

OVERVIEW	
Intended Application	Powering Devices
Model Type	Power Cords
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61

<b>PHYSICAL</b>	
Color	Black
Style	Power Cables
<b>CONNECTIONS</b>	
Connector A	IEC-320-C14
Connector B	 NEMA 5-15R
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

## Related Items

### Optional Products

Product Type	Related Model	Description	Qty.
Power Cables	<a href="#">P004-006</a>	6-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)	1
Power Cables	<a href="#">P006-006</a>	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2191](http://www.tripplite.com/en/products/model.cfm?txtModelID=2191).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.