



Powering Business Worldwide

2-ft. Power Cord (IEC-320-C14 to NEMA 5-15R)

MODEL NUMBER: P002-002-R



Highlights

- UL-listed
- Retail packaging

System Requirements

- A monitor with an AC power cord (NEMA 5-15P)
- A computer with an available power receptacle (IEC-320-C13)

Package Includes

- 2-ft. AC power adapter cord PC style male (IEC-320-C14) to AC female (NEMA5-15R)

Description

Tripp Lite makes your PC installation one step easier. This 2-ft. AC Power Adapter Cord allows you to plug a power cord with an NEMA 5-15P into an IEC-320-C13 outlet in a PDU or CPU. Installation with convenience is the name of the game. Features a NEMA 5-15R receptacle with an IEC-320-C14 plug. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail package.

Features

- UL-listed
- This 2 foot cord allows you to plug a power cord with an NEMA 5-15P into an IEC-320-C13 outlet in a PDU or CPU
- Frees up a wall outlet
- Plug type: IEC-320-C14 to NEMA 5-15R
- 16AWG SJT, 12A, 125V
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

| OVERVIEW | |
|-----------------------------|---|
| UPC Code | 037332042279 |
| Device Compatibility | Computer; Monitor/HDTV; PDU; Printer; Server; UPS |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 13 |
| Voltage Compatibility (VAC) | 125 |
| CONNECTIONS | |

| | |
|-------------------------------------|---------------------------|
| Side A - Connector 1 | IEC-320-C14 |
| Side B - Connector 1 | NEMA 5-15R |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Wire Gauge (AWG) | 16AWG |
| Wire Gauge (OD - mm²) | 1.31 |
| Cable Length (ft.) | 2 |
| Cable Length (m) | 0.61 |
| Shipping Dimensions (hwd / in.) | 6.75 x 5.75 x 2.00 |
| Shipping Dimensions (hwd / cm) | 17.14 x 14.60 x 5.08 |
| Shipping Weight (lbs.) | 0.40 |
| Shipping Weight (kg) | 0.18 |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| High Voltage | No |
| Locking Plug | No |
| Coiled Power Cord | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.