



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: P004-002-13RA

### AC Power Extension Cable - C13 Right Angle to C14 - 2 ft.

#### Highlights



- UL-listed
- C13 Right Angle - C14
- 18AWG (0.824mm), SJT, 10A, 100-250V

#### Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This handy 2ft. cord can be used to extend the power cord on any PC or device with a C14 plug. Features an IEC-320-C14 to IEC-320-C13 Right Angle connection. UL listed.

#### Package Includes

- 2-ft. universal AC power extension PC style male (IEC-320-C14) to PC style female (IEC-320-C13) Right Angle

#### Features

- UL-listed
- 2-ft. power extension cord for your PC or device with a C14 plug
- Plug type: IEC-320-C14 (male), to IEC-320-C13 (female) Right Angle
- 18AWG (0.824mm), SJT, 10A, 100-250V

#### Specifications

| OVERVIEW             |                  |
|----------------------|------------------|
| Intended Application | Powering Devices |
| Model Type           | Power Cords      |
| INPUT                |                  |
| Cable Length (ft.)   | 2                |
| Cable Length (m)     | 0.61             |
| PHYSICAL             |                  |
| Color                | Black            |
| Style                | Power Cables     |
| CONNECTIONS          |                  |

|  |                           |
|--|---------------------------|
| <b>Connector A</b>                         | IEC-320-C14               |
| <b>Connector B</b>                         | C13 RIGHT-ANGLE           |
| <b>Number of Connectors</b>                | 2                         |
| <b>WARRANTY</b>                            |                           |
| <b>Product Warranty Period (Worldwide)</b> | Lifetime limited warranty |

## Related Items

### Optional Products

| Product Type | Related Model                 | Description   | Qty. |
|--------------|-------------------------------|---|------|
| Power Cables | <a href="#">P004-002-13LA</a> | AC Power Extension Cable - C13 Left Angle to C14 - 2'         | 1    |
| Power Cables | <a href="#">P004-002-5</a>    | 5-Pack of 2-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13) | 1    |
| Power Cables | <a href="#">P004-004</a>      | 4-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)           | 1    |
| Power Cables | <a href="#">P004-006</a>      | 6-ft. 18AWG Power cord (IEC-320-C14 to IEC-320-C13)           | 1    |
| Power Cables | <a href="#">P004-006-2C13</a> | 6-ft. AC Power Extension Splitter Cable ( C14 to 2 x C13 )    | 1    |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4633](http://www.tripplite.com/en/products/model.cfm?txtModelID=4633).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.