



HDMI Send/Receive Pass-Through Wallplate, White (F/F)

MODEL NUMBER: P166-001-P





Highlights

- Feed Through HDMI Wallplate
- Helps keep Home Theater installations clean
- HDMI v1.3 and HDCP compliant

Package Includes

 HDMI Send/Receive Pass-Through Wallplate

Description

With this HDMI Send/Receive Pass-Through Wallplate, you can now hide that HDMI cable that's connected to the HDTV hanging on the wall by running the cable behind the wall and into the back of the face plate. Then connect a cable from your DVR or satellite/cable box into the front of the face plate with no unsightly cable dangling down from your TV. If your DVR or box is located a long distance from the HDTV, use P166-001-A active wall plate with signal booster.

Features

- Cleans up Home Theater installations by hiding HDMI Cables
- Simple Feed-Through design
- Standard electrical outlet size
- HDMI Female/Female connection
- HDMI v1.3 and HDCP Compliant

Specifications

OVERVIEW	
UPC Code	037332141026
Product Type	Pass-Through
Technology	HDMI
VIDEO	
Video Input	HDMI (FEMALE)
Video Output	HDMI (FEMALE)
Max Supported Video Resolution	1920 x 1080 (1080p @ 60Hz); 2560 × 1440 @ 60 Hz
HDR Support	No





AUDIO		
Audio Input	HDMI	
Audio Output	HDMI	
Audio Specification	Dolby TrueHD; DTS-HD Master Audio	
POWER		
Power Over Cable (PoC) Support	No	
CONNECTIONS		
Side A - Connector 1	HDMI (FEMALE)	
Side B - Connector 1	HDMI (FEMALE)	
Daisy-chainable / Cascadable	No	
PHYSICAL		
Color	White	
Material of Construction	Plastic	
Form Factor/Mounting Options	Wallplate	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.09	
Shipping Weight (kg)	0.04	
COMMUNICATIONS		
Signal Range (ft.)	50	
Signal Range (m)	15	
IR Remote Extension Support	No	
RS-232 Serial Extension Support	No	
USB Extension Support	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.