

DisplayPort to HDMI Adapter Cable (M/M), 3 ft. (0.9 m)

MODEL NUMBER: P582-003



Connect a Computer with Displayport to a HDMI enabled TV

Features

- 3-ft. Displayport to HDMI Adapter cable
- Supports 1080P video, as well as audio (if video card enabled)
- HDCP compatible
- In-line Passive adapter
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

Specifications

| OVERVIEW | |
|--------------------------------|---------------------|
| UPC Code | 037332186195 |
| Product Type | Passive Cable |
| Technology | HDMI; DisplayPort |
| Cable Type | Passive |
| VIDEO | |
| Max Supported Video Resolution | 1920 x 1200 (1080p) |
| CONNECTIONS | |
| Side A - Connector 1 | DISPLAYPORT (MALE) |
| Side B - Connector 1 | HDMI (MALE) |

Highlights

- Supports 1080P 1920x1080 resolution
- Supports Audio
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

System Requirements

- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P582-003-V2

Package Includes

- 3-ft. Displayport to HDMI Adapter cable



Powering Business Worldwide

TRIPP LITE
SERIES

| PHYSICAL | |
|-------------------------------------|----------------------------|
| Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Outer Diameter (OD) | 6.5mm |
| Wire Gauge (AWG) | 28 |
| Cable Length (ft.) | 3 |
| Cable Length (m) | 0.91 |
| Cable Length (in.) | 36 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.17 |
| Shipping Weight (kg) | 0.08 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.